



SP Static Recessed Lensed

2x2, 2 Lamp CF40, Prismatic Acrylic Lens

2x2, 2 Lamp CF40, Prismatic Acrylic Lens

The SP Static Lensed Troffer is a specification grade recessed lensed luminaire and offers many premium options.

Product data

General Information	
Lamp Source Code	FLU
Lamp Watts	40
Lamp Envelope Code	TT5
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed franse vertaling
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft

Product Data	
Order product name	2x2, 2 Lamp CF40, Prismatic Acrylic Lens
Commercial Code	2SPG2CF40R-FS01-1/2-EB
Order code	2SPG2CF40R-FS01-1/2-EB
Catalog Number Description	2x2, 2 Lamp CF40, Prismatic Acrylic Lens
Service / Spec Smart	-
Material Nr. (12NC)	DAY70000123