



# EvoGrid Recessed LED

2x2, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse

2x2, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse

EvoGrid Recessed Architectural LED provides general lighting perfect for a wide variety of applications. Its soft opal diffuser with large luminous area minimizes apparent brightness compared to other based luminaires.

## Product data

General Information	
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Luminaire Input Watts	30
Voltages	120/277/347/UNIV V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square

Initial Performance (IEC Compliant)	
Luminaire Lumens	3000
Product Data	
Order product name	2x2, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse
Commercial Code	2EVG30L835-2-D-UNV-DIM
Order code	2EVG30L835-2-D-UNV-DIM
Catalog Number Description	2x2, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse
Service / Spec Smart	Service Smart (2 Days) USA
Material Nr. (12NC)	DAY70000385