



SofTrace Recessed LED

2x2 Tunable White, 4400 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

2x2 Tunable White, 4400 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

Product data

General Information	
Color Temperature	6500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Luminaire Input Watts	48
Voltages	120/277/347/UNIV V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square

Initial Performance (IEC Compliant)	
Luminaire Lumens	4400
Product Data	
Order product name	2x2 Tunable White, 4400 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)
Commercial Code	2STG44L8TW-2-D-UNV-DTW
Order code	2STG44L8TW-2-D-UNV-DTW
Catalog Number Description	2x2 Tunable White, 4400 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)
Service / Spec Smart	-
Material Nr. (12NC)	DAY70000446