



# EvoGrid Recessed LED

2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

EvoGrid Recessed Architectural LED provides general lighting perfect for a wide variety of applications. Its soft opal diffuser with large luminous area minimizes apparent brightness compared to other based luminaires.

## Product data

General Information	
Color Temperature	6500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Luminaire Input Watts	46
Voltages	120/277/347/UNIV V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular

Initial Performance (IEC Compliant)	
Luminaire Lumens	4900
Product Data	
Order product name	2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)
Commercial Code	2EVG49L8TW-4-D-UNV-DTW
Order code	2EVG49L8TW-4-D-UNV-DTW
Catalog Number Description	2x4 Tunable White, 4900 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)
Service / Spec Smart	-
Material Nr. (12NC)	DAY70000460