



RBX LED High Bay

20,000 Nominal Delivered Lumens, 3500K, 80 CRI, 22" Clear Acrylic Short Reflector

20,000 Nominal Delivered Lumens, 3500K, 80 CRI, 22" Clear Acrylic Short Reflector - 129 lm/W

The RBX LED high bay luminaires have the familiar look and feel of traditional high bay luminaires. Available with acrylic or aluminum reflectors and a variety of lumen packages and color temperatures, the RBX is ideal for retail, industrial, and commercial applications.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Luminaire Input Watts	158
Voltages	120/208/240/277/347/UNIV V
Mechanical and Housing	
Fixture Size	22 in
Shape	Round

Initial Performance (IEC Compliant)	
Luminaire Lumens	20000
Efficacy	129 lm/W
Product Data	
Order product name	20,000 Nominal Delivered Lumens, 3500K, 80 CRI, 22" Clear Acrylic Short Reflector
Commercial Code	RBX20L835-ARR22S
Order code	RBX20L835-ARR22S
Catalog Number Description	20,000 Nominal Delivered Lumens, 3500K, 80 CRI, 22" Clear Acrylic Short Reflector
Service / Spec Smart	-
Material Nr. (12NC)	DAY70000495