



RBX LED High Bay

15,000 Nominal Delivered Lumens, 3500K, 80 CRI, 16" White Acrylic Reflector

15,000 Nominal Delivered Lumens, 3500K, 80 CRI, 16" White Acrylic Reflector - 135 lm/W

The RBX LED high bay luminaires have the familiar look and feel of traditional high bay luminaires. Available with acrylic or aluminum reflectors and a variety of lumen packages and color temperatures, the RBX is ideal for retail, industrial, and commercial applications.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Luminaire Input Watts	131
Voltages	120/208/240/277/347/UNIV V
Mechanical and Housing	
Fixture Size	16 in
Shape	Round

Initial Performance (IEC Compliant)	
Luminaire Lumens	15000
Efficacy	135 lm/W
Product Data	
Order product name	15,000 Nominal Delivered Lumens, 3500K, 80 CRI, 16" White Acrylic Reflector
Commercial Code	RBX15L835-ARR16SL
Order code	RBX15L835-ARR16SL
Catalog Number Description	15,000 Nominal Delivered Lumens, 3500K, 80 CRI, 16" White Acrylic Reflector
Service / Spec Smart	-
Material Nr. (12NC)	DAY70000506