



EvoGrid Recessed LED

2x4, 4300 Nominal Delivered Lumens, 80 CRI, 4000K, Round Diffuse, Standard Efficacy

2x4, 4300 Nominal Delivered Lumens, 80 CRI, 4000K, Round Diffuse, Standard Efficacy - 124 lm/W

EvoGrid Recessed Architectural LED provides general lighting perfect for a wide variety of applications. Its soft opal diffuser with large luminous area minimizes apparent brightness compared to other based luminaires.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	4300
Color Temperature	4000K	Efficacy	124 lm/W
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Luminaire Input Watts	35	Order product name	2x4, 4300 Nominal Delivered Lumens, 80 CRI, 4000K, Round Diffuse, Standard Efficacy
Voltages	120/277/347/UNIV V	Commercial Code	2EVG43L840-4-R-UNV-DIM
		Order code	2EVG43L840-4-R-UNV-DIM
		Catalog Number Description	2x4, 4300 Nominal Delivered Lumens, 80 CRI, 4000K, Round Diffuse, Standard Efficacy
		Material Nr. (12NC)	DAY70000770
Mechanical and Housing			
Fixture Size	2 ft x 4 ft		
Shape	Rectangular		