

Site & Area

PureForm

LED post top with comfort optic

Gardco PureForm LED post top features a sleek, low profile design. Comfort optics are designed to enhance visual comfort by reducing glare. Type 1, 2, 3, and 5 optical distributions are available with lumen output up to 9000 lumens. A full range of control options provides additional energy savings. Optional integral emergency battery backup is available for path-of-egress illumination.



Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

# Ordering guide

# example: PPT-140L-450-NW-G2-T3-1-UNV-DGY

Prefix PPT		Number of LEDs	Drive (	Current	LED Colo	r - Gene	eration	Mou	inting		D	listribution	Emerge	ncy		Voltage
•	eForm t top, nfort optics	140L 140 LEDs	450 650 1150 1675 2100	450 mA 650 mA 1150 mA <sup>1</sup> 1675 mA <sup>1</sup> 2100 mA <sup>12</sup>	NW-G2 CW-G2	70 CRI Neutra 70 CRI Cool W 70 CRI Warm 270 0K Genera Direct	White 3000K, Generation 2 al White 4000K, Generation 2 Vhite 5000K, Generation 2 Yellow ¢, 80 CRI ation 2 <sup>3</sup> Amber (590nm) ation 2 <sup>3</sup>	T3 T2	Mounts to a 3" Tenon (standa Mounts to a 2- Tenon (must bu ordered and st a separate acco	rd) 3/8" x 4 e iipped a	<sup>1"</sup> 3 as 5	Comfort Type 1 Comfort Type 2 Comfort Type 3 Comfort Type 5	b EBPC E b cr EBP E	lank for no attery mergency attery pack old weather mergency attery pack		120      120V        208      208V        240      240V        277      277V        347      347V        480      480V        UNV      120-277V (50/60Hz)        HVU      347-480V        (50/60Hz)
Options Dimming				Motion sensir	Ĵ		Photo-sensing			Electri				Finish		
DD FAWS SW LLC3 BL	Field Adjus Interface m Integral wir #3 lens <sup>4,5,6,</sup>	odule for SiteWise <sup>4,6</sup> eless module with	,8	IMRI3 Inte	egral with	#3 lens	TLRD5 Twist L	ock R ock R ock R			Sing Dou Can	le (120, 277, 347VAC) <sup>9</sup> ble (208, 240, 480VAC adian Double Pull 8, 240, 480VAC) <sup>9</sup>	) a	MGY Me	ite nze k Gray dium G	.,
DynaDin CS50 CM50 CE50 DA50 CS30 CM30 CE30 DA30	Security 50 Median 50 Economy 5 All Night 50 Security 30 Median 30 Economy 3	atic Profile Dimming ' % Dimming, 7 hours % Dimming, 8 hours 0% Dimming, 9 hours 0% Dimming, 9 hours % Dimming, 8 hours 0% Dimming, 9 hours 0% Dimming								Surge SP2		ction (10kA standard) eased 20kA		CC Cus (Mu	cify op or or R/ tom co ist sup	tional AL (ex: RAL7024)

1. 1150, 1675, and 2100mA not available with emergency battery backup (EBP).

2. 2100mA not available with emergency battery backup cold weather (EBPC).

3. Extended lead times apply. Contact factory for details.

- 4. Not available with other control options.
- Not available with motion sensor.
  Not available with photocontrol.
- Not available with photoconti
  Not available in 347 or 480V.
- 8. Available only in 120 or 277V.

- 9. Must specify input voltage.
- 10. Dimming will not be connected to NEMA receptacle if ordering
- with other control options.
- 11. Not available in 480V



PureForm Accessories (order separately)

PPT-T2

Post top tenon adapter for 2 3/8" x 4"

LED Wattage and Lumen Values

		LED		Average		Type 1			Type 2			Type 3		Type 5		
	Total	Current	Color	System	Lumen	BUG	Efficacy									
Ordering Code	LEDs	(mA)	Temp.	Watts	Output	Rating	(LPW)									
PPT-140L-450-NW-G2-x-UNV	140	450	4000	22	1971	B1-U0-G1	88	1951	B1-U0-G1	87	2421	B1-U0-G1	109	2254	B1-U0-G1	101
PPT-140L-650-NW-G2-x-UNV	140	650	4000	30	2636	B1-U0-G1	87	2609	B1-U0-G1	86	3237	B1-U0-G1	106	3014	B2-U0-G1	99
PPT-140L-1150-NW-G2-x-UNV	140	1150	4000	52	4736	B2-U0-G2	91	4686	B2-U0-G2	90	5816	B2-U0-G2	111	5415	B3-U0-G2	104
PPT-140L-1675-NW-G2-x-UNV	140	1675	4000	75	6574	B3-U0-G3	87	6506	B2-U0-G2	86	8074	B2-U0-G3	106	7517	B3-U0-G2	99
PPT-140L-2100-NW-G2-x-UNV	140	2100	4000	96	7871	B3-U0-G3	82	7789	B3-U0-G3	81	9011	B3-U0-G3	94	8999	B3-U0-G2	94

Values from photometric tests performed in accordance with IESNA LM-79 and are representative of the configurations shown. Actual performance may vary due to installation and environmental variables, LED and driver tolerances, and field measurement considerations. It is highly recommended to confirm performance with a photometric layout.

NOTE: Some data may be scaled based on tests of similar (but not identical) luminaires. Contact factory for configurations not shown.

LED Wattage and lumen values (Emergency Mode)

										Lumen C	Dutputs			
		LED	LED		Avg. System Watts		Type 1		Type 2		Type 3		Type 5	
		Current	Color	Temp. Range	Normal	Emergency	Normal	Emergency	Normal	Emergency	Normal	Emergency	Normal	Emergency
Ordering Code	LED Qty	(mA)	Temp.	(°C)	Mode	Mode	Mode	Mode	Mode	Mode	Mode	Mode	Mode	Mode
PPT-140L-450-NW-G2-x-EBP-UNV	140	450	4000	0 to 40	22	10	1971	1526	1951	1510	2421	1747	2254	1744
PPT-140L-650-NW-G2-x-EBP-UNV	140	650	4000	0 to 40	30	10	2636	1526	2609	1510	3237	1747	3014	1744
PPT-140L-450-NW-G2-x-EBPC-UNV	140	450	4000	-20 to 40	22	18	1971	2178	1951	2155	2421	2493	2254	2490
PPT-140L-650-NW-G2-x-EBPC-UNV	140	650	4000	-20 to 40	30	18	2636	2178	2609	2155	3237	2493	3014	2490
PPT-140L-1150-NW-G2-x-EBPC-UNV	140	1150	4000	-20 to 40	52	18	4736	2178	4686	2155	5816	2493	5415	2490
PPT-140L-1675-NW-G2-x-EBPC-UNV	140	1675	4000	-20 to 40	75	18	6574	2178	6506	2155	8074	2493	7517	2490


For emergency EBPC and EBP option, publish values are based on initial lumens.

## **Predicted Lumen Depreciation Data**

Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions.  $L_{70}$  is the predicted time when LED performance depreciates to 70% of initial lumen output. Calculated per IESNA TM21-11. Published  $L_{70}$  hours limited to 6 times actual LED test hours


Ambient Temperature °C	Driver mA	Calculated L <sub>70</sub> Hours	L <sub>70</sub> per TM-21	Lumen Maintenance % at 60,000 hrs
25°C	up to 2100mA	>100,000 hours	>60,000 hours	>84%

# Dimensions – Post Top Luminaire



# **Optical Distributions**

Based on 20' mounting height




# Asymmetric Optical Orientation Information

# **Standard Optic Position**

### Aimed Between The Yoke Supports

Luminaires ordered with asymmetric optical systems in the standard optic position will have the optical system oriented as shown below:

Symbol to indicate the direction of the street side



# **Specifications**

#### Housing

Two-piece sealed enclosure with main part of the housing designed as the structural and heat sink frame, enclosed by cover to give its unique form. It also includes yoke arm with arm covers. All die-cast parts are made of low-copper, die-cast aluminum alloy for a high resistance to corrosion. The sleek profile with optimized surface area allows housing to provide excellent convection heat transfer with minimum use of heat fins, giving the freedom to have a clean minimalist aesthetic design. Luminaire housing rated to IP66, tested in accordance to Section 9 of IEC 60598-1.

#### Vibration resistance

Luminaire is tested and rated 3G over 100,000 cycles conforming to standards set forth by ANSI C136.31-2010. Testing includes vibration to 3G acceleration in three axes, all performed on the same luminaire.

#### Light engine

Light guide technology provides low-glare, uniform illumination. Composed of 140 LEDs strategically positioned on the edge of the optical plate. Light engine luminous opening size optimized to best achieve a balance between lumen output and optical performance with the need to provide visual comfort. Light engine frame ensures contact with housing to provide heat conduction and sealing against the elements. Light engine is RoHS compliant. . Standard color temperatures: 3000K +/- 130K, 4000K+/- 130K, 5000K +/- 225K. Minimum CRI of 70. Also available in 2700K and Amber (>590nm) with extended lead times. Contact factory for details.

#### Energy saving benefits

System efficacy up to 111 lms/W with significant energy savings over Pulse Start Metal Halide luminaires. Optional control options provide added energy savings during unoccupied periods.

#### **Optical systems**

The advanced LED comfort optical system provides Types 1, 2, 3, and 5. Composed of high performance UV-stabilized optical grade lens with molded micro-optics to achieve desired distribution optimized to get a exceptional lighting uniformity. Performance tested per LM-79 and TM-15 (IESNA) certifying its photometric performance. Luminaire designed with 0% uplight (U0 per IESNA TM-15).

#### Mounting

PureForm Post Top mounts standard to a  $3" \times 4"$  Tenon, but can also be mounted to a 2-3/8" x 4" Tenon if a separate sleeve is ordered as an accessory.

#### **Control options**

**0-10V dimming (DD):** Access to 0-10V dimming leads supplied through the yoke of the luminaire (for secondary dimming controls by others). Cannot be used with other control options.

SiteWise (SW): SiteWise system includes a controller fully integrated in the luminaire that enables the luminaires to communicate with a dimming signal transmitter cabinet located on site using patented central dimming technology. A locally accessible mobile app allows users to access the system and set functionalities such as ON/OFF, dimming levels and scheduling. SiteWise is available with motion response options in order to bring the light back to 100% when motion is detected. Cannot be used with other control options or photocell options. Additional functionalities are available such as communication with indoor lighting and connection to BMS systems. Complete information on the control system can be found on the SiteWise website at signify.com/sitewise. Field Adjustable Wattage Selector (FAWS): Luminaire equipped with the ability to manually adjust the wattage in the field to reduce total luminaire lumen output and light levels. Comes pre-set to the highest position at the lumen output selected. Use chart below to estimate reduction in lumen output desired. Cannot be used with other control options or motion response.

FAWS Position	Percent of Typical Lumen Output
1	25%
2	50%
3	55%
4	65%
5	75%
6	80%
7	85%
8	90%
9	95%
10	100%

Note: Typical value accuracy +/- 5%


Automatic Profile Dimming (CS/CM/CE/CA): Standard dimming profile of 30% or 50% provide flexibility towards energy savings goals while optimizing light levels during specific dark hours. When used in combination with not programmed motion response it overrides the controller's schedule when motion is detected. After 5 minutes with no motion, it will return to the automatic diming profile schedule. Automatic dimming profile scheduled with the following settings:


- CS50/CS30: Security for 7 hours night duration (Ex., 11 PM 6 AM)
- CM50/CM30: Median for 8 hours night duration (Ex., 10 PM 6 AM)
- CE50/CE30: Economy for 9 hours night duration (Ex., 9 PM 6 AM)
- CA50/CA30: for all night (during all dark hours)
- Cannot be used with other control options.

**Emergency Battery Backup (EBP/EBPC):** Emergency battery packs included integral to the luminaire, allowing for a consistent look between emergency and non-emergency luminaires. EBP is suitable for use in ambient temperature conditions from 0°C (-32°F) to 40°C (100°F) available on 450mA and 650mA only. EBPC cold weather rated down to -20°C (-4°F) available on all wattage except the 2100mA configuration. Both systems are designed to have a secondary driver with relay to immediately detect AC power loss to power luminaire for a minimum of 90 minutes from the time power is lost. Available with 120-277V, or 'UNV' only.

Wireless system (LLC): Optional wireless controller integral to luminaire ready to be connected to a Limelight system (sold by others). The system allows you to wirelessly manage the entire site, independent lighting groups or individual luminaires while on-site or remotely. Based on a high-density mesh network with an easy to use web-based portal, you can conveniently access, monitor and manage your lighting network remotely. Wireless controls can be combined with site and area, pedestrian, and parking garage luminaires as well, for a completely connected outdoor solution. Equipped with motion response with #3 lens (LLC3) for 8-25' mounting heights. Also available with remote pod accessory where pod is mounted separate from luminaire to pole or wall.

# LLC3/LLCR3 Luminaire or remote mount controller with #3 lens






#### Motion response options

**Bi-Level Infrared Motion Response (BL-IMRI3):** Motion Response module is mounted integral to luminaire factory pre-programmed to 50% dimming when not ordered with other control options. P50-IMRI is set/ operates in the following fashion: The motion sensor is set to a constant 50%. When motion is detected by the PIR sensor, the luminaire returns to full power/light output. Dimming on low is factory set to 50% with 5 minutes default in "full power" prior to dimming back to low. When no motion is detected for 5 minutes, the motion response system reduces the wattage by 50%, to 50% of the normal constant wattage reducing the light level. Other dimming settings can be provided if different dimming levels are required. This can also be done with FSIR-100 Wireless Remote Programming Tool (contact Technical Support for details).

Infrared Motion Response with Other Controls (SW-IMRI3): When used in combination with other controls (Automatic Dimming Profile and SiteWise), motion response device will simply override controller's schedule with the added benefits of a combined dimming profile and sensor detection. In this configuration, the motion response device cannot be re-programmed with FSIR-100 Wireless Remote Programming Tool. The profile can only be re-programmed via the controller.

**Infrared Motion Response Lenses (IMRI3):** Infrared Motion Response Integral module is available lens #3 (IMRI3), which is designed for mounting heights up to 20' with a 40' diameter coverage area. See chart for approximate detection patterns:

# IMRI3 Luminaire or remote mount controller with #3 lens



#### Electrical

Twist-Lock Receptacle (TLRD5/TLRD7/ TLRPC): Twist Lock Receptacle with 5 pins enabling dimming or with 7 pins with additional functionality (by others) can be used with a twistlock photoelectric cell or a shorting cap. Dimming Receptacle Type B (5-pin) and Type D-24 (7-pin) in accordance to ANSI C136.41. Can be used with third-party control system. Receptacle located on top of luminaire housing. When specifying receptacle with twistlock photoelectric cell, voltage must be specified.

**Driver:** Driver efficiency (>90% standard). 120-480V available (restrictions apply). Open/short circuit protection. Optional 0-10V dimming to 10% power. RoHS compliant.

Button Photocontrol (PCB): Button style design for internal luminaires

mounting applications. The photocontrol is constructed of a high impact UV stabilized polycarbonate housing. Rated voltage of 120V or 208–277V with a load rating of 1000 VA. The photocell will turn on with 1–4Fc of ambient light.

Surge protection (SP1/SP2): Each luminaire is provided as standard with surge protector tested in accordance with ANSI/IEEE C62.45 per ANSI/ IEEE C62.41.2 Scenario I Category C High Exposure 10kV/5kA waveforms for Line Ground, Line Neutral and Neutral Ground, and in accordance with U.S. DOE (Department of Energy) MSSLC (Municipal Solid-State Street Lighting Consortium) Model Specification for LED Roadway Luminaires Appendix D Electrical Immunity High Test Level 10kV / 5kA. Optional 20kV is available for additional protection.

#### Listings

UL/cUL wet location listed to the UL 1598 standard, suitable for use in ambient temperatures from -40° to 40°C (-40° to 104°F). Most PureForm PPT comfort configurations are qualified under Standard DesignLights Consortium<sup>®</sup> category. Consult DLC Qualified Products list for more details.

#### Finish

Each standard color luminaire receives a fade and abrasion resistant, electrostatically applied, thermally cured, triglycidal isocyanurate (TGIC) textured polyester powdercoat finish. The surface treatment achieves a minimum of 1000 hours for salt spray resistant finish in accordance with testing performed and per ASTM B117 standard. Standard colors include bronze (BZ), black (BK), white (WH), dark gray (DGY), and medium gray (MGY). Consult factory for specs on optional or custom colors.

#### Warranty

PureForm luminaires feature a 5-year limited warranty. See signify.com/warranties for complete details and exclusions.

# Signify

2019 Signify Holding B.V. All rights reserved. Signify reserves the right to make shanges in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

Signify, North America Corp., 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216 Signify, Canada Ltd., 281 Hillmount Rd, Markham, ON Canada L6C 2S3 Tel. 800-668-9008