



Recessed

PureFX


1'x4', 3600 lm 3000/3500/4000K



Project:	
Spec Type:	
Catalog No:	9414DxxxLx36
Qty	
Line Notes:	

Using Ledalite's revolutionary MesoOptics technology, PureFX offers the perfect blend of brightness, control and energy efficiency.

Ordering guide



* Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration. † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Integrated Controls Please indicate with check mark.

Flex Whip (6' length)

Upgrades & Accessories Please indicate with check mark.

Drywall Kit

Response Daylight Single Zone (DS)



Optical System

The optical frame assembly consists of an acrylic panel with a layer of protected MesoOptics film which efficiently provides a luminous, controlled, low glare 3-dimensional batwing distribution. The optical frame ends are constructed from die–formed cold–rolled steel assembled together with extruded aluminum profiles in a sturdy frame. The frame is hinged to allow easy access to the inside of the fixture. Maintenance can be performed from below the ceiling.

Housing

Die-formed, post-painted, 22 gauge cold-rolled steel housing. Multiple wire entrances are available (top or side) to allow continuous row mounting of fixtures. Optional frame restraint is available to provide additional safety support.

Mounting

Compatible with lay-in acoustical ceilings using an exposed 9/16", 15/16" or slot T-grid suspension system (NEMA types G, NFG & NFGS). Integral mounting tabs are provided which handle different T-grid heights.

Finish

Housing and Frame: Post-painted, high quality powder coat. Available in white only.

Weight

Maximum 25lb .

Electrical

LED boards are easily field replaceable. Fixtures are factory pre-wired and tested for all circuits. Driver access from below the ceiling. Optional armored cable flex whips are supplied in 6' lengths.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 900lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: **Reported** methodology is L70 (12k) >52,000 hrs.

Source Color

LEDs rated for standard color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Available with integrated Response Daylight sensor, which dims the luminaire when daylight is present. Contact Philips Ledalite for additional functionality.

Approvals

Certified to UL, IES & CSA Standards. City of Chicago Approved CCEA (housing option C). Type IC Rated.

Warranty

Five-year luminaire limited warranty including LED boards and driver. www.philips.com/warranties.


Environment

Rated for dry or damp locations in operating ambient temperatures of 0-25°C (32-77°F). Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty. Not suitable for natatorium environments.


Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Options and Details

Mounting




Cross Section






Photometry @ CRI>80, 3500K



0% Up / 100% Down



All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: F46Z-744C4T (2/7/2012) Model Number: 9*14D***LB36

Type: Surface-mounted or recessed troffers

Candela Distribution

Vertical	Horizontal Angle				Zonal	
Angle	0	22.5	45	67.5	90	Lumens
0	1212	1212	1212	1212	1212	0
5	1214	1215	1217	1216	1220	116
15	1189	1204	1241	1274	1291	352
25	1120	1162	1247	1320	1352	571
35	978	1042	1150	1226	1254	705
45	753	810	903	965	980	685
55	523	559	622	673	684	550
65	312	335	379	412	418	372
75	136	165	196	213	208	197
85	26	43	48	49	46	52
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

RCR	Ceiling:		8	0			70			50		0
KCK	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		109	105	101	97	107	103	99	98	95	93	85
2		100	92	85	80	97	90	84	87	82	77	72
3		91	81	73	67	89	80	72	77	70	65	61
4		84	72	64	57	81	71	63	68	61	56	52
5		77	65	56	49	75	63	55	61	54	49	45
6		71	58	49	43	69	57	49	55	48	43	40
7		66	53	44	38	64	52	44	50	43	38	35
8		62	48	40	34	60	47	39	46	39	34	31
9		57	44	36	31	56	44	36	42	35	30	28
10		54	41	33	28	53	40	33	39	32	28	26

Avg. Luminance (cd/m2)

Vertical	H	orizontal Ang	įle
Angle	0	45	90
55	3142	3736	4109
65	2544	3090	3408
75	1810	2609	2769
85	1028	1897	1818

Distribution Summary

Hemisphere	0% Up / 100% Down	
Spacing Along (0°)	1.29	
Spacing Across (90°)	1.52	

Optical Performance

Flux (lm)	3623	3600	3494
Efficacy (lm/W)	83.7	83.7	81.8
Power (W)	43.3	43.0	42.7
ССТ (К)	4012	3472	3073
CRI	83	83	83
R9	24	22	21
x	0.3825	0.4109	0.4358
У	0.3860	0.4023	0.4107
Duv	0.0040	0.0040	0.0030

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	347V			
Input Power	43.0W	37.8W			
Input Current	0.36A	0.11A			
Power Factor	0.992	0.970			
Total Harm. Distortion		9.0%			
Tested values contact technical support for rated values					

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.

© 2018 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008