


SmartBright Direct Panel


RC093V

Mounting instruction/安裝說明書

V1.1




Product Type 產品型號	Dimension(mm) 尺寸(mm) LxWxH (mm)	LEDs 顆粒	CCT (K) 色溫	Power(W) 功率	Lumen Output(lm) 流明輸出	Voltage 電壓	Frequency 頻率	kg
RC093V LED26S/840 PSU W60L60 TW	603x603x35	42	4000	24	2600	100-240V~	50/60Hz	1.8
RC093V LED26S/865 PSU W60L60 TW	603x603x35	42	6500	24	2600			
RC093V LED36S/840 PSU W60L60 TW	603x603x35	54	4000	33	3600			
RC093V LED36S/865 PSU W60L60 TW	603x603x35	54	6500	33	3600			




W60L60

Recessed/嵌入式




Adjust the luminaire position to fit ceiling well
安裝並調整好燈具位置

Safety chain / 安全繩



The product should install safety chain
(Safety chain is not included).
本產品需要安裝安全繩
(本產品不含安全繩)

Wiring Method/接線方式




Min : 3x0.75mm²

Max : 3x1.5mm²

N: Blue/藍色

L : Brown/棕色

⊕ : Yellow & Green/黄绿色



委製/進口商：台灣飛利浦照明股份有限公司
地址：台北市南港區園區街3-1號15樓之一
產地：荷蘭飛利浦照明授權於中國製造
電話：0800-808-268

PHILIPS


SmartBright Direct Panel

RC093V


Mounting instruction/安裝說明書

V1.1

PCV / 石膏板安裝




石膏板開口尺寸 cutout size
W60L60 : 580*580mm(+/-2mm)
石膏板厚度/Suggested ceiling thickness :
8mm~16mm



Springs are not included in package.
If the customer need to use, please buy it.
PCV Accessory 12 NC: 9114 017 24242
包裝內不含PVC彈簧配件，如果需要，請另行購買，12NC為9114 017 24242

Safety chain / 安全繩



The product should install safety chain
(Safety chain is not included).
本產品需要安裝安全鏈 (本產品不含安全鏈)

Product Type /產品型號	Run Current (A) /輸入電流 (A)		Start (Inrush) Current(A) /Ipeak (A) /衝擊電流 (A)		Start Current Duration (μs) /T(@50% of Ipeak) (μs) /衝擊電流脈衝寬度(μs)		* Touch current or protective conductor current (mA) /接觸電流(漏電流) 或保護導體電流 (mA)		Maximum Number of Luminaire on MCB 16A Type B (pcs) /B型16A微型斷路器 允許連接此燈具數量(pcs)		Maximum Number of Luminaire on MCB 16A Type C (pcs) /C型16A微型斷路器 允許連接此燈具數量(pcs)	
	100V	240V	100V	240V	100V	240V	100V	240V	100V	240V	100V	240V
RC093V LED26S/840 PSU W60L60 TW	0.3	0.13	4.32	5.52	24.00	26.4	<3		25	50	25	50
RC093V LED26S/865 PSU W60L60 TW	0.3	0.13	4.32	5.52	24.00	26.4	<3		25	50	25	50
RC093V LED36S/840 PSU W60L60 TW	0.4	0.17	3.60	7.52	36.3	36.8	<3		20	40	20	40
RC093V LED36S/865 PSU W60L60 TW	0.4	0.17	3.60	7.52	36.3	36.8	<3		20	40	20	40

The leakage current *(touch current or protective conductor current) of electrical circuit may be greatly dependent upon electrical supply cables used such as its rating and length, proper connection of electrical supply cables to luminaires and wiring connection topology of luminaires to the supply electrical circuit amongst other site conditions.

* In some cases referred to as Earth Leakage Current.

Please read this manual carefully before using the product.



1. For indoor use only.
2. Do not switch on before complete installation.
3. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
4. If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.
5. The luminaire shall not be covered with thermal insulation or similar material under any circumstance.
6. The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
7. The luminaire is complied with IEC 60598 and GB 7000.
8. The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc. must be avoided during the use and storage.



在使用產品前請仔細閱讀這個安裝說明書：

1. 僅適用於室內燈具；
 2. 接線過程中，切勿通電；
 3. 此燈具應由有資格的電工安裝，接線要符合IEE電氣標準或國家標準；
 4. 如果此燈具的外部軟纜或軟線損壞了，該線要由製造商或其服務代理商或一個類似的有資格的人來更換，以避免發生危險；
 5. 燈具不能被隔熱或類似材料覆蓋；
 6. 此燈具的光源應由製造商或其服務代理商或一個類似的有資格的人來更換；
 7. 此燈具是依據IEC60598所製造；
 8. 此燈具避免在腐蝕性環境或者含有有害物質，例如硫化物，鹵化物，鄰苯二甲酸酯等環境中存儲和使用。
 9. 限用物質含有情況標示資訊請參考飛利浦網址<http://www.deco.philips.com.tw/RoHS>
- 維修方式：
若燈具出現故障，請立即停止使用並關閉電源，聯絡專業人員處理。