

Linear

MicroSquare gen2 wall

1300 lm/4ft, Direct
3000/3500/4000K



Project: _____

Spec Type: _____

Catalog No: 2221LxKLN

Qty _____

Line Notes: _____

Philips Ledalite's MicroSquare gen2 has been re-engineered to furnish your space with the highest quality, discreet, narrow lines of continuous light. Elegant, low glare illumination with wide-throw upper and lower distributions improve visual comfort while allowing increased fixture spacing. This in turn, helps reduce initial and operating costs.

Ordering guide

Product Type	Source	Color Temp *	Lumens *	Lower Optics	Upper Optics	Run Length	Wiring †	Voltage	Driver	Finish
2221	L		K	L	N					
MicroSquare II Direct	L LED	A 4000K B 3500K C 3000K	G 2600 lm/4ft K 1300 lm/4ft	L Flush Silk Lens	N Solid Housing	04 4' 06 6' 08 8' XX Total run length (4' increments)	7 1cct Dimming M 1cct Dimming + EM Wiring	1 120V 2 277V 3 347V	E Philips Advance	W Standard White T Titanium Silver B Black C Custom

* Nominal values within a range. Consult photometry data for exact color temp, lumens & distribution.

† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Mounting Hardware

Wall	Mount Type	Consult separate mounting spec sheet for mount type options
------	------------	---

Endcaps -



SC - Solid Cube
(standard)



SB - Sculpted
Black Acrylic



FM - Flush Maple

MicroSquare gen2 wall

1300 lm/4ft, Direct
3000/3500/4000K

Optical System

Upper hemisphere: Light from a linear array of upward-facing LEDs is shaped into a homogeneous, wide-throw batwing distribution using either a freeform elliptical lens or an engineered light guide panel.
Lower hemisphere: Light from a linear array of downward-facing LEDs is diffused through a transmissive white engineered acrylic lens to deliver a highly uniform, luminous continuum without sacrificing efficacy.

Endcaps

Cubic aluminum endcaps with an internal draw-tight connector to minimize the joint line.
Three styles available: solid cube, sculpted black acrylic insert or flush maple insert.

Finish

Standard finish is a textured matte powder coat in white, black or titanium silver.

Housing

Precision aluminum extrusion, post painted.

Weight

Maximum: Surface & Suspended Direct or Indirect - 7.5 lb/4ft; Suspended D/I - 9.5 lb/4ft; Wall D/I - 13.8 lb/4ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100% (347V: 5-100%), Class 2 rated output.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 **Reported** methodology is:
L80 (12k) >72,000 hrs.

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and color accuracy within 2 SDCM.

Mounting

Suspended: Tamper-resistant aircraft cable gripper provides unlimited vertical adjustment. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements.
Wall: A hidden steel rail and bracket system attaches the housing to the wall structure. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½" on center and within 12" of an end or joint.
Surface: Fixture is mounted flush to surface using hidden brackets at ends and joints.

Approvals

Certified to UL, CSA and IES standards.
Certain suspended indirect/direct versions are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty

Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties.


Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section


Wall Direct




MicroSquare gen2 wall

1300 lm/4ft, Direct
3000/3500/4000K


Dimensions - Modules




Optics and Styles



Sculpted Black Acrylic



Flush Maple




Solid Cube

MicroSquare gen2 wall

1300 lm/4ft, Direct
3000/3500/4000K

Photometry - 3500K



Candela Distribution

Vertical Angle	0	Horizontal Angle	22.5	45	67.5	90	Zonal Lumens
0	476	476	476	476	476	476	0
5	474	474	473	474	474	474	45
15	458	455	457	456	456	456	129
25	424	419	422	421	420	419	194
35	375	371	373	371	369	369	233
45	315	312	312	310	309	309	240
55	246	244	243	240	240	240	217
65	170	169	167	165	165	165	165
75	91	90	90	90	90	90	95
85	21	22	23	23	23	23	26
90	0	0	0	0	0	0	0
95	0	0	0	0	0	0	0
105	0	0	0	0	0	0	0
115	0	0	0	0	0	0	0
125	0	0	0	0	0	0	0
135	0	0	0	0	0	0	0
145	0	0	0	0	0	0	0
155	0	0	0	0	0	0	0
165	0	0	0	0	0	0	0
175	0	0	0	0	0	0	0
180	0	0	0	0	0	0	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08
IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

RCR	Ceiling	Wall	70	50	30	10	70	50	30	50	30	10	0
0	119	119	119	119	116	116	116	111	111	111	111	100	0
1	109	104	100	96	106	102	98	97	94	91	84	84	0
2	99	90	84	78	96	89	82	85	80	75	69	69	0
3	90	79	71	65	87	78	70	75	68	63	58	58	0
4	82	70	61	55	80	69	61	66	59	53	50	50	0
5	76	63	54	47	74	62	53	59	52	46	43	43	0
6	70	56	47	41	68	56	47	54	46	40	38	38	0
7	65	51	42	36	63	50	42	49	41	36	33	33	0
8	60	47	38	32	59	46	38	45	37	32	30	30	0
9	56	43	35	29	55	42	34	41	34	29	27	27	0
10	53	40	32	26	52	39	31	38	31	26	24	24	0

Avg. Luminance (cd/m2)

Vertical Angle	0	Horizontal Angle	45	90
55	7396	7303	7210	
65	6930	6804	6720	
75	6035	5966	5966	
85	4073	4480	4480	

Distribution

Hemisphere	0% Up / 100% Down
Glare Control	Meets RP-1-12 recommendations for VDT-Critical spaces
Spacing Along (0 °)	1.25
Spacing Across (90 °)	1.24

LED

lighting facts®

A Program of the U.S. DOE

Philips Ledalite

Light Output (Lumens)

1343

Watts

13.2

Lumens per Watt (Efficacy)

101.74

Color Accuracy

Color Rendering Index (CRI)

84

Light Color

Correlated Color Temperature (CCT)

3487 (Bright White)

Warm White

Bright White

Daylight

2700K

3000K

4500K

6500K

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: F46Z-17R6M8 (3/6/2017)

Model Number: 22x1LBKLN

Type: Luminaire - Linear

MicroSquare gen2 wall

1300 lm/4ft, Direct
3000/3500/4000K

Optical Performance

Nominal CCT:	3000K	3500K	4000K
Flux (lm)	1303	1344	1340
Efficacy (lm/W)	98.0	101.8	100.8
Power (W)	13.3	13.2	13.3
CCT (K)	3107	3487	4128
CRI	84	84	84
R9	11	9	13
x	0.4288	0.4063	0.3748
y	0.3998	0.3920	0.3728
Duv	-0.0010	0.0000	0.0000

Electrical Performance - 3500K

Input Voltage	120V	277V
Input Power	13.2W	13.2W
Input Current	0.11A	0.05A
Power Factor	0.985	0.941
Total Harm. Distortion	12.2%	17.0%
Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.		

