ColorBlast 6

The original compact exterior LED wash luminaire with intelligent color light

Date:	i	
Type:	:	
Firm 1	Name:	
Projec	ect:	

High-performance ColorBlast 6 LED luminaires generate rich, saturated colors and color-changing effects for a range of wall-washing and floodlighting applications. Designed with the needs of lighting designers and architects in mind, ColorBlast 6 can be used in both indoor and outdoor installations. High-intensity LEDs produce superior light output in a compact, low-profile housing. ColorBlast 6 also offers full pan and tilt rotation, flexible mounting options, two beam angles, and superior control through Color Kinetics or third-party controllers.

- Two beam patterns—A frosted glass lens (21° beam angle) produces a soft-edge beam, while a clear glass lens (10° beam angle) affords extended light projection.
- Outdoor rated—Fully sealed for maximum luminaire life and IP66-rated for outdoor applications, ColorBlast 6 luminaires meet or exceed specifications for use in wet locations. Rugged, die-cast aluminium housing is available in white or black powder-coated finish.
- Flexible mounting options—The versatile luminaire canopy base can be mounted to a junction box or directly to a wall, ceiling, or floor. A liquid-tight cable fitting seals the canopy opening for use in damp or wet environments.

Beam Angle	10°, 21°
Lumens*	534 to 584
Efficacy	13 to 14.2
LED Channels	Red/Green/Blue



Input Voltage	24 VDC via PDS-150e or PDS-60			
Power Consumption	25 W			
Weight	2.95 kg (6.5 lb)			
Housing Material	Die-cast aluminium, black or white powder-coated finish			
Approbations	UL/cUL, FCC Class A, CE, PSE, CQC, C-Tick, SAA			
Environment	Dry/Damp/Wet Location, IP66			
Applications	Flood Lighting, Spot Lighting, Wall Washing			

Specification Sheets

* Lumen output measurements comply with IES LM-79-08 testing procedures.

PDF Download		Lumens*	Efficacy	Item Number	12 NC
10° Clear Lens, Black Housing		584	14.2	116-000026-03	910503700596
10° Clear Lens, White Housing	10°	584	14.2	116-000026-02	910503700595
21° Frosted Lens, Black Housing	21°	534	13	116-000026-01	910503700594
21° Frosted Lens, White Housing		534	13	116-000026-00	910503700593

