


by (s) ignify

Floodlight

Designer Floodlight

DF7 - 7"

The Gardco Designer Floodlight DF7 is a flood luminaire with a choice of (5) precision faceted optical systems. Each is designed to provide a specific distribution and sharp cutoff of stray light. The contemporary soft form diecast housing is available in a variety of finishes creating compatibility with most architectural and landscape elements. The high strength diecast aluminum knuckle features an integral splice compartment eliminating the need for a supplementary junction box and thereby permitting closer to grade mounting.



Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notos:	

Ordering Guide example: DF7CHFL70MH120BRPPCB

Prefix DF7	Moun	ting	Distr	ibution	Wattage		Voltage	Finish		Options	
DF/											
DF7	n C	Stub-up Conduit Mount For direct mounting to (2) 1/2" GRC or IMC conduits. No j-box required. J-Box Mount For mounting into 1/2" (1.27cm) hub. Also suitable for direct surface mount to walls	HFL VFL HSP	Flood Vertical Flood	Pulse Start MH Magnetic Ballast	70MH 200MH¹(Ē) 100MH³ 175PSMH¹,2(Ē)	120 208 240 277	BRP BLP WP NP	Bronze Paint Black Paint White Paint Natural	BD ⁶	Button Type Photocontrol Barn Doors Cutoff Hood
	or	or ceilings when fed by EMT, BX, SJO, NM, etc. (For surface mount over outlet box.	пог	Spot	High Pressure	<u>.</u>	347 UNIV ³ BGP VP		Aluminum Paint		Polycarbonate Shield
	W Wall/Ceiling Canopy Mount For mounting over (not to) a 4" recessed outlet box. When mounted on vertical surface, provides vertical aiming from straight down to 100° up from nadir. When mounted on a vertical surface, long axis of luminaire must be horizontal (+/-30"). Mounts directly to wall or ceiling. The surface structure must be suitable to support the luminaire. Only suitable for use on non-combustable surfaces.	For mounting over (not to) a 4" recessed	NSP		Sodium Magnetic Ballast	100HPS 150HPS			ESB ⁹	Fusing Extended Splice Box Wire Guard	
		2		E Wattages marked meet federal ener standards applic through 500 wat luminaires only.	ergy efficiency cable to 150 watt		ос				
	WMB	Wall Mount Bullhorn For mounting over (not to) a 4" (10.16cm) recessed outlet box. Provides full axial 180° vertical and 358" rotational aiming. Mounts direct to wall. Surface structure must be suitable to support the assembly. Outer end of WMB must be in the "straight up" position, as shown in diagram on opposite page. Luminaire mounts with the knuckle below the body of the luminaire only.						sc	ex: OC-RAL7024. Special Color Paint Specify. Must supply color chip.		
	W90	Wall Arm Mount For mounting over (not to) a 4" (10.16cm) recessed outlet box. Provides full axial 180° vertical and 358' rotational aiming range. Mounts direct to wall. Surface structure must be suitable to support the luminaire. When mounted in wet locations, luminaire must be mounted as shown in diagrams on page 2. In damp or dry locations, arm assembly may be inverted.									
otnote	ST	Stanchion Mount 18"(45.72cm) stanchion for in-ground concrete burial mounting. Minimum 6" in concrete.									
he uide or	SM	Surface Mount Stanchion For mounting to 18" (45.72cm) stanchion pole assembly.									

#4 nor in the ordering guide of

There's fo

footnote Enter the order code into the appropriate box above. Note: Gardco reserves the right to refuse a configuration. Not all combinations and configurations are valid. Refer to notes below for exclusions and limitations. For questions or concerns, please consult the factory.

- 1. Utilizes mogul based lamps (T15, E18 or E28). Available with VFL, HSP, and NSP distributions only. Not available with PCB, POLY, F or ESB options.
- 2. Not available in 347V.
- 3. Not available in 480V.
- 5. Not Available with 175PSMH or 200MH.
- . Barn Doors (BD) and Cutoff Hoods (CH) are painted to match the luminaire. Either can be used concurrently with the POLY option.
- 7. Not Available with WG option.
- 8. 120V through 277V only.
- Supplied standard with 175PSMH and 200MH luminaires. Not available for use as additional splicing volume with 175PSMH or 200MH luminaires.
- 10. Not Available with BD, CH and POLY options. Field Installable.
- 11. Polycarbonate lenses carry a 1 year warranty only.

Designer Floodlight DF7 - 7"

Additional Mounting Accessories

РТА	Pole top 2 3/8" (6.03cm) tenon adapter			
TAB	B Twin arm bracket for use with ST or PTA			
PT2	Pole top 2 3/8" (6.03cm) tenon adapter for twin back to back luminaire mounting			

Specifications

HOUSING

A single-piece aluminum housing is die cast in a soft barrel form. A one piece extruded gasket mates with door frame.

DOOR/LENS ASSEMBLY

A heat and impact resistant 3/16" (.48cm) tempered glass lens and one piece silicone gasket are mechanically secured to door frame.

KNUCKLE

The die cast aluminum knuckle features an integral splice compartment. A single captive 3/16" (.48cm) stainless steel

allen-head bolt and stainless steel nut securely lock the knuckle aiming teeth in 5° increments. An opposite cover plate is removable for access to splices. The knuckle assembly is fully gasketed.

OPTICAL SYSTEM

The wide flood, vertical flood and horizontal spot optical systems are homogenous sheet and extruded aluminum, electrochemically brightened, anodized and sealed. The narrow spot reflector is hydroformed faceted Alzak® aluminum.

ELECTRICAL

HID UNITS: Each high power factor ballast is the separate component magnetic type capable of providing reliable lamp starting to -20°F/-29°C.

LAMPHOLDER

The pulse rated socket is glazed porcelain with nickle plated screw shell. All sockets are medium base except 175PSMH and 200MH units.

FINISH

Each luminaire receives a fade and abrasion resistant, electrostatically applied,

thermally cured textured, polyester powdercoat finish.

LABELS

All luminaires bear UL or CUL (where applicable) Wet Location labels.

WARRANTY


Gardco luminaires feature a 5 year limited warranty. See Warranty Information on www.sitelighting.com for complete details and exclusions. Polycarbonate lenses carry a 1 year warranty only.

DF7 Splice Compartment Capacity	Standard Units	Extended Splice Box	175PSMH and 200MHUnits
#12 AWG Conductors ¹²	5	9	5
TAB #10 AWG Conductors ¹²	3	7	3
12. Including ground.			

DF7 Pole Loading Data	EPA
Single Luminaire on PTA Adapter	1.3 ft²/.12m²
Twin Luminaires on PTA Adapter	1.9 ft²/.18m²
Twin Luminaires on TAB Adapter	2.8ft ² /.26m ²

Designer Floodlight DF7 - 7"

Dimensions and Mounting DF7-C DF7-J 70-150w units 175PSMH and 200MH units 16.00" 16.00" 40.64cm 40.64cm 9.00" 9.00" 22.86cm 22.86cm 13.38" 13.38" 33.99cm 33.99cm 180° 358° ├ 7.00" ┤ - 9.50" 17.78cm 24.13cm 29.19" 36.00" (2) DF7 (Luminaires only)* 74.14cm 66.04cm TAB Twin Arm Bracket* PTA - Pole Top PT2 - Twin Pole Adaptor* Top Adaptor* ST-18" Stanchion* RSA4 Pole with 2 3/8" x 4" Tenon RSA4 Pole with 24.00" (6.03cm X 10.16cm) 2 3/8" x 4" Tenon 60.96cm (Specify Height) * Order mounting accessories separately. (6.03cm X 10.16cm) (Specify Height)



(s) ignify

5.00" -12.70cm