# PHILIPS

### Linear

Sona suspended (2LC Up, Dn)


3500 lm/4ft 60%-70% Up 3000/3500/4000K



Project: Spec Type: Catalog No: 7725LxEAA Qty Line Notes:

Incredible efficacy & boundless lighting choices mean the re-engineered Sona suspended LED is destined to become a future classic. Flexible up/ down distributions and tailored LED optics mean you always have the right light for every task.


#### Ordering guide



\* Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.

† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

#### **Mounting Hardware**





3500 lm/4ft 60%-70% Up 3000/3500/4000K

#### **Optical System**

1 Light Chamber Upper: Lateral-facing LED arrays deliver light into both the upper and lower hemispheres, giving a highly efficient, native 70% up / 30% down distribution with a wide, homogeneous upper batwing distribution. A fully indirect version with a solid lower housing can be specified, as well as a 50% down-light kit option. 1 Light Chamber Lower: A downward-facing LED array

aims light into the lower hemisphere, for a highly efficient, fully direct distribution or optional 80% down version. **2 Light Chambers:** Both lateral-facing and downwardfacing LED arrays are combined in separate upper and lower chambers for the ultimate in up/down distribution control.

Lenses: On the upper surface an engineered diffuser smooths the light distribution on the ceiling and acts as a dust cover. On the lower surface, two 4" wide optics are available: either a curved, engineered acrylic diffuse lens flush to the housing; or a white louver with regressed diffuser for improved high angle cut-off and visual comfort.

#### **Endcaps**

Diecast aluminum endcaps, either Sculpted (curved) or Flat.

#### Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including pacific aqua, are available on request. White sensors only.

#### Housing

Precision formed 18 gauge cold-rolled steel. Cross section size (approx.): 2.6"h x 9"w (suspended) or 7.4"w (wall mount).

#### Weight

Maximum: Suspended 4.9lb/ft, Wall 3.4lb/ft

#### Electrical

Factory pre-wired to section ends with quick-wire connectors.

#### **Standard Drivers**

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

#### **Standard Battery Pack**

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: suspended 1400lm, wall 1200lm.

#### Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is:  $L_{80}$  (12k) >72,000 hrs (**Reported** methodology)  $L_{80}$  (12k) 110,000 hrs (**Projected** methodology).

#### Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

#### Controls

Suspended version (1 light chamber only) available with the following integrated controls: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

\*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to www.philips.com/spacewise

#### Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Variable mounting along the length of the housing is available for certain configurations upon request. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½' on center and within 6" of an end or joint.

#### **Joints**

Self-aligning, gasketed joining system wth hands-free wiring feature.

#### Approvals

Certified to UL, CSA and IES standards. Most suspended versions (except 1 light chamber down with louver) are DesignLights Consortium<sup>®</sup> qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

#### Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties

#### Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

#### Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


#### **Dimensions - Cross Section**



3500 lm/4ft 60%-70% Up 3000/3500/4000K

#### **Dimensions - Modules**

Suspended - Side view, no end caps



#### **Optics and Styles**


	A	Curved Acrylic Lens
V White Louver		

3500 lm/4ft 60%-70% Up 3000/3500/4000K

#### Photometry @ CRI>80, 3500K

# $90^{-1}_{-1}$

63% Up / 37% Down



All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product lest data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: F46Z-SOW5N7 (5/5/2017) Model Number: 7725LBEAA Type: Luminaire - Linear

#### Candela Distribution

Vertical		Zonal				
Angle	0	22.5	45	67.5	90	Lumens
0	455	455	455	455	455	0
5	449	453	453	454	455	43
15	432	436	436	437	438	123
25	399	402	402	404	405	185
35	352	355	355	356	357	222
45	294	296	299	299	300	230
55	227	230	232	234	235	207
65	155	158	161	163	164	159
75	81	84	90	96	97	95
85	18	24	34	42	45	38
90	1	8	17	24	26	0
95	34	45	50	53	53	55
105	114	142	174	192	191	178
115	209	285	378	424	433	350
125	307	426	593	697	721	491
135	359	458	619	744	781	460
145	376	436	546	632	660	336
155	384	412	473	526	545	218
165	388	397	418	442	450	120
175	390	390	388	389	390	38
180	384	384	384	384	384	0

Coefficients of Utilization (%)												
RCR	Ceiling: Wall:	70	8 50	0 30	10	70	70 50	30	50	50 30	10	0 0
0		104	104	104	104	94	94	94	76	76	76	37
1		95	90	86	83	85	82	79	66	64	62	30
2		86	79	72	67	78	71	66	58	54	51	25
3		78	69	62	56	71	63	56	51	46	42	21
4		71	61	53	47	64	55	49	45	40	36	18
5		65	54	46	40	59	49	42	40	35	31	16
6		60	48	40	35	54	44	37	36	31	27	14
7		56	43	36	30	50	40	33	33	27	23	12
8		51	39	32	26	47	36	29	30	24	21	11
9		48	36	28	23	43	33	26	27	22	18	10
10		45	33	26	21	40	30	24	25	20	17	9

#### Avg. Luminance (cd/m2)

	•	'
н	orizontal Ang	le.
0	45	90
3558	3440	3408
3279	3130	3112
2763	2678	2777
1798	2316	2732
	0 3558 3279 2763	3558 3440 3279 3130 2763 2678

#### Distribution

Hemisphere	63% Up / 37% Down
Peak/Zenith	2.07
Peak Output	794 cd
Glare Control	Meets RP-1-12 recommendations for VDT-Critical spaces

Values per 4ft unit

IESNA LM-79-08 IES files for this and other photometric options can be downloaded online at

Fixture photometry has been

conducted in accordance with

www.lightingproducts.philips.com

#### 25 399 402 35 352 355

3500 lm/4ft 60%-70% Up 3000/3500/4000K

#### Optical Performance @ 120V

Nominal Spec:	3000K	3500К	4000K
Flux (lm)	3390	3546	3626
Efficacy (lm/W)	125.1	130.8	133.3
Power (W)	27.1	27.1	27.2
CCT (K)	3020	3378	3958
CRI	84	83	84
R9	11	9	11
x	0.4361	0.4138	0.3835
У	0.4048	0.3976	0.3820
Duv	0.0003	0.0012	0.0016

#### Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V			
Input Power	27.1W	27.5W	28.6W			
Input Current	0.23A	0.11A	0.09A			
Power Factor	0.989	0.938	0.945			
Total Harm. Distortion 11.6% 15.7% 16.0%						
Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.						

© 2017 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008