




Incredible efficacy & boundless lighting choices mean the re-engineered Sona suspended LED is destined to become a future classic. Flexible up/down distributions and tailored LED optics mean you always have the right light for every task.

Ordering guide



^{*} Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.

Mount Type Consult separate mounting spec sheet for mount type options: Ledalite Suspended Mounting Options Endcaps - Integrated Controls Please indicate with check mark. Response Daylight Single Zone (DS) SpaceWise DT Occupancy & Daylight Sensor (SZ)



 $[\]dagger$ Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

2200 lm/4ft, Direct 3000/3500/4000K

Optical System

 $\label{light Chamber Upper: Lateral-facing LED arrays deliver light into both the upper and lower hemispheres, giving a highly efficient, native 70% up / 30% down distribution with a wide, homogeneous upper batwing distribution. A fully indirect version with a solid lower housing can be specified, as well as a 50% down-light kit option.$

1 Light Chamber Lower: A downward-facing LED array aims light into the lower hemisphere, for a highly efficient, fully direct distribution or optional 80% down version.

2 Light Chambers: Both lateral-facing and downwardfacing LED arrays are combined in separate upper and lower chambers for the ultimate in up/down distribution control.

Lenses: On the upper surface an engineered diffuser smooths the light distribution on the ceiling and acts as a dust cover. On the lower surface, two 4" wide optics are available: either a curved, engineered acrylic diffuse lens flush to the housing; or a white louver with regressed diffuser for improved high angle cut-off and visual comfort.

Endcaps

Diecast aluminum endcaps, either Sculpted (curved) or Flat

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including pacific aqua, are available on request. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel. Cross section size (approx.): $2.6\text{''}h \times 9\text{''}w$ (suspended) or 7.4''w (wall mount).

Weight

Maximum: Suspended 4.9lb/ft, Wall 3.4lb/ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: suspended 1400lm, wall 1200lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L_{80} (12k) >72,000 hrs (**Reported** methodology) L_{80} (12k) 110,000 hrs (**Projected** methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Suspended version (1 light chamber only) available with the following integrated controls: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/

advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible
Android phone and Philips Field App. Compatible
wireless dimming wall switches are available for dimming.

347V is not available as a standard option. For more

information, please refer to www.philips.com/spacewise

Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Variable mounting along the length of the housing is available for certain configurations upon request. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to $4\frac{1}{2}$ on center and within 6" of an end or joint.

Joints

Self-aligning, gasketed joining system with hands-free wiring feature.

Approvals

Certified to UL, CSA and IES standards. Most suspended versions (except 1 light chamber down with louver) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties

Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


Dimensions - Cross Section




2200 lm/4ft, Direct 3000/3500/4000K

Dimensions - Modules

Suspended - Side view, no end caps





Optics and Styles




2200 lm/4ft, Direct 3000/3500/4000K

Photometry @ CRI>80, 3500K







Candela Distribution

Vertical			izontal A 45		00	Zonal
Angle	0	22.5		67.5	90	Lumens
0	1052	1052	1052	1052	1052	0
5	1020	1031	1036	1046	1050	98
15	880	898	934	982	1004	264
25	695	722	781	861	905	363
35	491	527	601	698	758	382
45	289	330	419	516	578	327
55	154	168	247	327	370	226
65	96	102	121	160	180	131
75	49	52	59	67	69	64
85	13	15	21	22	19	22
90	1	6	12	12	5	0
95	1	4	7	8	6	7
105	2	6	6	7	7	6
115	1	8	8	9	9	7
125	1	5	12	11	11	8
135	1	4	11	14	14	7
145	1	3	8	10	10	4
155	1	2	5	8	7	2
165	1	2	3	5	4	1
175	1	2	2	2	1	0
180	1	1	1	1	1	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

DCD	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	110	110	110	98
1		110	106	102	99	107	104	100	99	96	94	85
2		102	95	89	84	99	93	87	89	84	80	74
3		94	85	78	72	91	83	77	80	74	70	65
4		87	76	69	63	85	75	68	72	66	61	57
5		81	69	61	55	79	68	61	66	59	54	51
6		75	63	55	49	73	62	55	60	53	48	45
7		70	58	50	44	68	57	49	55	49	44	41
8		66	53	45	40	64	52	45	51	44	40	37
9		62	49	42	37	60	49	41	47	41	36	34
10		58	46	38	34	57	45	38	44	38	33	31

Avg. Luminance (cd/m2)

Vertical	H	orizontal Ang	gle
Angle	0	45	90
55	2407	3652	5384
65	2024	2358	3417
75	1687	1761	1970
85	1228	1438	1184

Distribution

Hemisphere	2% Up / 98% Down		
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces		
Spacing Along (0°)	0.92		
Spacing Across (90°)	1.18		

2200 lm/4ft, Direct 3000/3500/4000K

Optical Performance @ 120V

Nominal Spec:	3000K	3500K	4000K
Flux (lm)	1821	1920	1967
Efficacy (lm/W)	94.4	99.5	101.9
Power (W)	19.3	19.3	19.3
CCT (K)	2957	3448	3810
CRI	82	82	83
R9	2	3	6
x	0.4388	0.4106	0.3923
у	0.4027	0.3984	0.3921
Duv	0.0009	0.0021	0.0038

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	19.3W	19.3W	20.0VV
Input Current	0.16A	0.07A	0.06A
Power Factor	0.993	0.964	0.967
Total Harm. Distortion	8.4%	12.2%	12.0%

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).

