Product Id	Model No.	Primary Use	Classification
PUPR9XUT	APX08L135-(UNV120208240277)-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
P2MU6RBH	APX08LL35-(UNV120208240277)-A-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
P7Q8JZMS	APX08LL35-(UNV120208240277)-M-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PUFPFZ5A	APX08LL35-(UNV120208240277)-N-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PPYY2QP4	APX08LL35-(UNV120208240277)-W-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
P92HV8PR	APX08LL35-347	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
P3Q83G95	APX08LL35-347-A	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PWVSCZ8P	APX08LL35-347-M	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PGCRNMBA	APX08LL35-347-N	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PTGVCP43 PW5NUWDR	APX08LL35-347-W APX08LL40-(UNV120208240277)-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings Low-Bay Luminaires for Commercial and Industrial Buildings	Standard Standard
PJTTXA7U	APX08LL40-(UNV120208240277)-A-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PE1NM8HA	APX08LL40-(UNV120208240277)-M-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
P2SY55YB	APX08LL40-(UNV120208240277)-N-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PP1VDNJW	APX08LL40-(UNV120208240277)-W-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PW77E8HW	APX08LL40-347	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PTC5KNGC	APX08LL40-347-A	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PEWKWCX3	APX08LL40-347-M	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PFQ1V642	APX08LL40-347-N	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
P5USZ3SW	APX08LL40-347-W	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PKYCAP5A	APX08LL50-(UNV120208240277)-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
P1JSJ8X2 PGB47YS4	APX08LL50-(UNV120208240277)-A-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings Low-Bay Luminaires for Commercial and Industrial Buildings	Standard Standard
PGB47YS4 PRKNQKS2	APX08LL50-(UNV120208240277)-M-(MD360WEMLED) APX08LL50-(UNV120208240277)-N-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PRRINGR32 P2R69TUW	APX08LL50-(UNV120208240277)-W-(MD360WEMLED)	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PNE59MVE	APX08LL50-347	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PP69KDWJ	APX08LL50-347-A	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PZ2HWMQR	APX08LL50-347-M	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PVKKSX3X	APX08LL50-347-N	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
PS9JXDXB	APX08LL50-347-W	Low-Bay Luminaires for Commercial and Industrial Buildings	Standard
P289G3P1	APX12LL35-(UNV120208240277)-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PS1FEUCR	APX12LL35-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PH1DHY6V	APX12LL35-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PDKNAB21	APX12LL35-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PWZDCJXN	APX12LL35-(UNV120208240277)-W-(MD360WEMLED) APX12LL35-347	High-Bay Luminaires for Commercial and Industrial Buildings	Standard Standard
PH7QSV3E PNJ6Y9R8	APA12LL35-347 APX12LL35-347-A	High-Bay Luminaires for Commercial and Industrial Buildings High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PSPQSVTB	APX12LL35-347-A	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PQCK4EHT	APX12LL35-347-N	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P3RF755G	APX12LL35-347-W	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P3XJF57N	APX12LL40-(UNV120208240277)-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PJ63FNPX	APX12LL40-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PGT45YDY	APX12LL40-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PWAUB3X1	APX12LL40-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P1K6RFT6	APX12LL40-(UNV120208240277)-W-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PQQP253D	APX12LL40-347	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PY9V1YYY	APX12LL40-347-A	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PCHZZJ94 PHW8W78J	APX12LL40-347-M APX12LL40-347-N	High-Bay Luminaires for Commercial and Industrial Buildings High-Bay Luminaires for Commercial and Industrial Buildings	Standard Standard
PEK1KWX7	APX12LL40-347-W	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PSWPRJTD	APX12LL50-(UNV120208240277)-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PA9FQJGR	APX12LL50-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PYXG2XAG	APX12LL50-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PD6CU3NV	APX12LL50-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PUH3N5EP	APX12LL50-(UNV120208240277)-W-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P977ZV7S	APX12LL50-347	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P8HV1Y47	APX12LL50-347-A	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P4DYQUWF	APX12LL50-347-M	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P32X9JK5	APX12LL50-347-N	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PZ6MU1SF	APX12LL50-347-W	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PHM54EAQ PUB2S2A6	APX16LL40-(UNV120208240277)-(MD360WEMLED) APX16LL40-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PUB2S2A6 PKS9WU3Q	APX16LL40-(UNV120208240277)-A-(MD360WEMLED) APX16LL40-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings High-Bay Luminaires for Commercial and Industrial Buildings	Standard Standard
PK59W03Q PKFU78H1	APX16LL40-(UNV120208240277)-N-(MD360WEMLED) APX16LL40-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PKF078H1 P9K5JUQX	APX16LL40-(UNV120208240277)-W-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PMBE1DCK	APX16LL40-347-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PNWQ6Q7C	APX16LL40-347-A-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PK9PC639	APX16LL40-347-M-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P8MUJPAE	APX16LL40-347-N-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PMZW5Y7H	APX16LL40-347-W-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PFJJ6PJS	APX16LL50-(UNV120208240277)-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
	APX16LL50-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P3JJ5SCY			
P3JJ5SCY PXZ7UXH2	APX16LL50-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P3JJ5SCY PXZ7UXH2 PX24BXJQ	APX16LL50-(UNV120208240277)-M-(MD360WEMLED) APX16LL50-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P3JJ5SCY PXZ7UXH2	APX16LL50-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	

Product Id	Model No.	Primary Use	Classification
PUWEU9PR	APX16LL50-347-A-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PSNPD7RP	APX16LL50-347-M-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PGYTKHYN	APX16LL50-347-N-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P1C158WD	APX16LL50-347-W-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PRXPM99X	APX20LL40-(UNV120208240277)-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PSNQ2DSR	APX20LL40-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PBWQCN9N	APX20LL40-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PWJH6P4C	APX20LL40-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PC9P7JQF	APX20LL40-(UNV120208240277)-W-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P9FFSU25	APX20LL40-347-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PG89ARC7	APX20LL40-347-A-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PCRKYT22	APX20LL40-347-M-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P6YH7F5D	APX20LL40-347-N-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P18MY3TY	APX20LL40-347-W-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PBTANDPZ	APX20LL40-480-LFA	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PS82D42R	APX20LL50-(UNV120208240277)-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PNNAS2DP	APX20LL50-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PHMCXQ8C	APX20LL50-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PXFB6H5F	APX20LL50-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P9A8CJV4	APX20LL50-(UNV120208240277)-W-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P96RV1EU	APX20LL50-347-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PQF6GN38	APX20LL50-347-A-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P7VNP5JN	APX20LL50-347-M-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P19GTUK3	APX20LL50-347-N-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P87W4UNH	APX20LL50-347-W-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P8FH859U	APX24LL40-(UNV120208240277)-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PUNWPM4U	APX24LL40-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PXNRSM2B	APX24LL40-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PVR9DQU1	APX24LL40-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PYR4YSP2	APX24LL40-(UNV120208240277)-W-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PC6UMW1A	APX24LL40-347-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PTE6QK1G	APX24LL40-347-A-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P3QRRZZ5	APX24LL40-347-M-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PUY59QT1	APX24LL40-347-N-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PBEJX836	APX24LL40-347-W-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P8EEBH2Y	APX24LL40-480	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PFY88Q9B	APX24LL50-(UNV120208240277)-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PKTSDH92	APX24LL50-(UNV120208240277)-A-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P41EPVJK	APX24LL50-(UNV120208240277)-M-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P9X6MSX1	APX24LL50-(UNV120208240277)-N-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
P6BPNVY8	APX24LL50-(UNV120208240277)-W-(MD360WEMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PA6413DD	APX24LL50-347-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PRPKDPHT	APX24LL50-347-A-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PBCT7WHG	APX24LL50-347-M-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PXNPQFRK	APX24LL50-347-N-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard
PSBH8KHR	APX24LL50-347-W-(EMLED)	High-Bay Luminaires for Commercial and Industrial Buildings	Standard