


PHILIPS

LUXSPACE

DN560B/561B/570B/571B




IP20

50Hz
60Hz


220V
AC




		A	B	C	CCT/CRI	P	P max	
DN560B/DN561B	LED8S	250mm	550mm	≥3mm	830/840	8 W	8,8 W	0,72 kg
DN560B/DN561B	LED12S	250mm	550mm	≥3mm	830/840	11,6 W	13 W	0,72 kg
DN560B/DN561B	LED12S	250mm	550mm	≥3mm	927/930	14 W	15,4W	0,72 kg
DN570B/DN571B	LED12S	300mm	700mm	≥3mm	830/840	11 W	12 W	1,17 kg
DN570B/DN571B	LED12S	300mm	700mm	≥3mm	927/930	13 W	14,4 W	1,17 kg
DN570B/DN571B	LED20S	300mm	700mm	≥3mm	830/840	17,6 W	19,4W	1,17 kg
DN570B/DN571B	LED20S	300mm	700mm	≥3mm	927/930	21,8W	24W	1,17 kg
DN570B/DN571B	LED24S	300mm	700mm	≥3mm	830/840	21,8W	24W	1,17 kg
DN570B/DN571B	LED24S	300mm	700mm	≥3mm	927/930	26,8W	29,6W	1,17 kg
DN570B/DN571B	LED40S	300mm	800mm	≥10mm	830/840	32,8W	36W	1,17 kg




	H [mm]	mm	Ø [mm]
DN560B	72	150	164
DN561B	86	150	164
DN570B	96.5	200	214
DN571B	119	200	214








1a




1b





2





2b




DN560B/561B/570B/571B + PG
DN560B/561B/570B/571B + PGO





DALI dimming range 1-100%



Inrush current
I mains (A)
I max
max/2
I nom.
Time (us)
Tref

	Xitanium 20W/m 0.15- 0.5A 54V 230V	Xitanium 36W/m 0.3- 1.05A 54V 230V	Xitanium 20W WH 0.15-0.5A 54V Is	Xitanium 36W WH 0.3- 1.05A 54V Is	Xitanium 20W WH 0.15-0.5A 54V TD/Is CL	Xitanium 36W WH 0.3- 1A 54V TD/Is CL	XITANIUM 36W/M 0.3- 1.05A 54V TD 230V
Inom (A)	0.12	0.2	0.11	0.19	0.11	0.19	0.2
Imax (A)	18	18	15.8	16	20.4	20.4	18
Tref (µs)	250	250	224	216	195	195	250
MCB	Max number of drivers						
B-10A	x21	x21	x21	x21	x15	x15	x21
B-16A	x34	x34	x36	x36	x24	x24	x34
C-10A	x34	x34	x34	x34	x24	x24	x34

CLO Version

			Pmax (W)	Pmax (W)
		CCT/CRI	@ t=0h	@ t=50kh
DN560B/DN561B	LED8S	830/840	6	8
DN560B/DN561B	LED12S	830/840	9	11,6
DN560B/DN561B	LED12S	927/930	11	14
DN570B/DN571B	LED12S	830/840	9	11
DN570B/DN571B	LED12S	927/930	10	13
DN570B/DN571B	LED20S	830/840	14	17,6
DN570B/DN571B	LED20S	927/930	23	28,8
DN570B/DN571B	LED24S	830/840	17	21,8
DN570B/DN571B	LED24S	927/930	21	26,8
DN570B/DN571B	LED40S	830/840	26	32,6

CLO Table		
Step	time (h)	P %
	0	80%
1	3000	81%
2	7000	83%
3	10000	84%
4	13000	85%
5	17000	87%
6	20000	88%
7	23000	89%
8	27000	91%
9	30000	92%
10	33000	93%
11	37000	95%
12	40000	96%
13	43000	97%
14	47000	99%
15	50000	100%



DO NOT REPROGRAM THE DRIVER
Constant light Output Option stopped @ 50 000h



©2017 Philips Lighting Holding B.V.
 All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.
 The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use.
 Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.
 The Netherlands