




Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately.

Reflector Trim	Reflector Trim		Height	Lamp
1090	1002	NON-IC	5-1/4" (133mm)	75W PAR30L
	1003RS	NON-IC REMODELER	5-1/4" (133mm)	75W PAR30L
	1000IC	IC	7-1/4" (184mm)	60W PAR30S
	1004ICN	NON-IC	7-1/2" (191mm)	75W PAR30S
	1004ICRS	NON-IC REMODELER	7-1/2" (191mm)	75W PAR30S
	1004ICXN	AirSeal® / IC	7-1/2" (191mm)	60W PAR30S

S = Short Neck Lamp
L = Long Neck Lamp

Caractéristiques

Housing: Hydroformed aluminum, .040" thick min. Non-yellowing, gloss white powder coat finish for permanent reflectivity and surface protection.

Flange: Frosted clear polycarbonate flange ring. Pull down and release for toolless relamping.

Glass: Pressed borosilicate glass textured diffuser. Meets NEC requirements for spas and hot tube. May be installed less than 7'-6" above max water surface height.


Markings

cULus listed, suitable for wet locations.

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	

Lentille décorative pour endroits mouillés

Ouverture du plafond : 5-1/4 po (133mm)



Le luminaire complet comprend la Garniture et le Cadre de montage : Choisir chacun séparément.

Garniture	Cadre de montage		Hauteur	Lampe
1090	1002	NON-ISOLÉ	5-1/4" (133mm)	75W PAR30L
	1003RS	NON-ISOLÉ RÉNOVATION	5-1/4" (133mm)	75W PAR30L
	1000IC	ISOLÉ (IC)	7-1/4" (184mm)	60W PAR30S
	1004ICN	NON-ISOLÉ	7-1/2" (191mm)	75W PAR30S
	1004ICRS	NON-ISOLÉ RÉNOVATION	7-1/2" (191mm)	75W PAR30S
	1004ICXN	AirSeal® / IC	7-1/2" (191mm)	60W PAR30S

S = Lampe à collet court

L = Lampe à collet long

Caractéristiques

Boîtier : hydroformé en aluminium, 0,40 po min. d'épaisseur.

Fini de peinture en poudre blanc lustré non jaunissant pour une réflectivité et une protection de la surface permanentes.

Bordure : anneau de bordure en polycarbonate clair dépoli.

Tirer vers le bas et relâcher pour un relampage sans outil.

Verre : diffuseur en verre borosilicaté texturé. Satisfait aux exigences

NEC pour les spas. Peut être installé à moins de 7 pi 6 po au-dessus de la hauteur maximale de la surface de l'eau.

Marquage

Homologué cULus ; convient aux endroits mouillés

Canlyte

3015 Louis-Amos, Lachine, Québec H8T 1C4 • (514) 636-0670 • Fax (514) 636-0460

www.canlyte.com

Information Projet

Type:

Nom Projet:

No. Cat.:

Lampe(s):

Notes:

PHILIPS
LIGHTOLIER®