

ATTESTATION OF CONFORMITY

Issued to : Philips (China) Investment Co., Ltd.
No.1602-1605, No.218 Tianmu W Rd, Shanghai City, 200072, P. R. China

For the product : LED waterproof luminaire

Trademark : PHILIPS

Type/Model : WT088C series; WT099C series; WT118C series
Please refer to Annex model list for details

Ratings : 220-240 V~; 50/60 Hz; max 46 W; Class I
Please refer to Annex model list for details

Manufactured by : Philips (China) Investment Co., Ltd.
No.1602-1605, No.218 Tianmu W Rd, Shanghai City, 200072, P. R. China

Requirements : EN 55015:2013
EN 61547:2009
EN 61000-3-2:2014
EN 61000-3-3:2013

This Attestation is granted on account of an examination by DEKRA, the results of which are laid down in a confidential file no. 3161848.50

This Attestation implies that the examined types are in accordance with the standards designated under the Electromagnetic compatibility directive 2004/108/EC.

The examination has been carried out on one single specimen of the product, submitted by the manufacturer. The Attestation does not include an assessment of the manufacturer's production. Conformity of his production with the specimen tested by DEKRA is not the responsibility of DEKRA.

Shanghai, 13 February 2015

Number: 3161848.01AOC

DEKRA Testing and Certification (Shanghai) Ltd.

C. Lin
Certification Manager



© Integral publication of this attestation and adjoining reports is allowed.

Page 1 of 3

Annex

Document no. : 3161848.01AOC

Type	Lamp	Power	LED driver	Enclosure colour
WT118C LED45 CW PSU L1500	2×(48×0.34W) +(24×0.34W) LED	46W	Xitanium 75W 0.12-0.4A 215V 230V	Dark grey
WT118C LED45 NW PSU L1500				
WT118C LED45 CW PSU L1500 ENG				
WT118C LED45 NW PSU L1500 ENG				
WT118C LED36 CW PSU L1200	2×(48×0.34W) LED	36W	PLS 36W 0.24A 150V 220-240V	Dark grey
WT118C LED36 NW PSU L1200				
WT118C LED36 CW PSU L1200 LI				
WT118C LED36 NW PSU L1200 LI				
WT118C LED36 CW PSU L1200 ENG				
WT118C LED36 NW PSU L1200 ENG				
WT118C LED18 CW PSU L1200	2×(44×0.2W) LED	20W	LED Driver 20W 0.28A 69V 230V PCB	Dark grey
WT118C LED18 NW PSU L1200				
WT118C LED18 CW PSU L1200 LI				
WT118C LED18 NW PSU L1200 LI				
WT118C LED18 CW PSU L1200 ENG				
WT118C LED18 NW PSU L1200 ENG				
WT118C LED18 CW PSU L600	(48×0.39W) LED	21W	LED Driver 20W 0.28A 69V 230V PCB	Dark grey
WT118C LED18 NW PSU L600				
WT118C LED18 CW PSU L600 LI				
WT118C LED18 NW PSU L600 LI				
WT118C LED18 CW PSU L600 ENG				
WT118C LED18 NW PSU L600 ENG				
WT118C LED9 CW PSU L600	(44×0.22W) LED	11W	PLS12-140-Fi- Linear	Dark grey
WT118C LED9 NW PSU L600				
WT118C LED9 CW PSU L600 LI				
WT118C LED9 NW PSU L600 LI				
WT118C LED9 CW PSU L600 ENG				
WT118C LED9 NW PSU L600 ENG				
WT088C LED28 CW PSU L1200	2×(30×0.42W) LED	28W	PLS 34W 0.3A 110V 220-240V	Light grey
WT088C LED28 NW PSU L1200				
WT088C LED28 CW PSU L1200 LI				
WT088C LED28 NW PSU L1200 LI				
WT088C LED14 CW PSU L1200	2×(40×0.19W) LED	17W	LED Driver 20W 0.28A 69V 230V PCB	Light grey
WT088C LED14 NW PSU L1200				
WT088C LED14 CW PSU L1200 LI				
WT088C LED14 NW PSU L1200 LI				

Annex

Document no. : 3161848.01AOC

Type	Lamp	Power	LED driver	Enclosure colour
WT088C LED18 CW PSU L600	(48×0.39W) LED	21W	LED Driver 20W 0.28A 69V 230V PCB	Light grey
WT088C LED18 NW PSU L600				
WT088C LED18 CW PSU L600 LI				
WT088C LED18 NW PSU L600 LI				
WT088C LED9 CW PSU L600	(44×0.22W) LED	11W	PLS12-140-Fi-Linear	Light grey
WT088C LED9 NW PSU L600				
WT088C LED9 CW PSU L600 LI				
WT088C LED9 NW PSU L600 LI				
WT099C LED45 CW PSU L1500	2×(48×0.34W)+(24×0.34W) LED	46W	Xitanium 75W 0.12-0.4A 215V 230V	Light grey
WT099C LED45 NW PSU L1500				
WT099C LED36 CW PSU L1200	2×(48×0.34W) LED	36W	PLS 36W 0.24A 150V 220-240V	Light grey
WT099C LED36 NW PSU L1200				
WT099C LED18 CW PSU L1200	2×(44×0.2W) LED	20W	LED Driver 20W 0.28A 69V 230V PCB	Light grey
WT099C LED18 NW PSU L1200				
WT099C LED18 CW PSU L600	(48×0.39W) LED	21W	LED Driver 20W 0.28A 69V 230V PCB	Light grey
WT099C LED18 NW PSU L600				
WT099C LED9 CW PSU L600	(44×0.22W) LED	11W	PLS12-140-Fi-Linear	Light grey
WT099C LED9 NW PSU L600				
WT118C LED45 CW PSD L1500	2×(48×0.34W)+(24×0.34W) LED	46W	Xitanium 75W 0.12-0.40A 215V TD 230V	Dark grey
WT118C LED45 NW PSD L1500				
WT118C LED45 CW PSD L1500 ENG				
WT118C LED45 NW PSD L1500 ENG				
WT118C LED36 CW PSD L1200	2×(48×0.34W) LED	36W	Xitanium 75W 0.12-0.40A 215V TD 230V	Dark grey
WT118C LED36 NW PSD L1200				
WT118C LED36 CW PSD L1200 ENG				
WT118C LED36 NW PSD L1200 ENG				
WT118C LED18 CW PSD L1200	2×(44×0.2W) LED	20W	Xitanium 36W 0.12-0.40A 110V TD 230V	Dark grey
WT118C LED18 NW PSD L1200				
WT118C LED18 CW PSD L1200 ENG				
WT118C LED18 NW PSD L1200 ENG				
WT118C LED18 CW PSD L600	(48×0.39W) LED	21W	Xitanium 36W 0.12-0.40A 110V TD 230V	Dark grey
WT118C LED18 NW PSD L600				
WT118C LED18 CW PSD L600 ENG				
WT118C LED18 NW PSD L600 ENG				
WT118C LED9 CW PSD L600	(44×0.22W) LED	11W	Xitanium 36W 0.12-0.40A 110V TD 230V	Dark grey
WT118C LED9 NW PSD L600				
WT118C LED9 CW PSD L600 ENG				
WT118C LED9 NW PSD L600 ENG				