



PHILIPS


TrueLine







SP530P












Dimensions in mm					Sensor/ Blind sensor holder.	
Suspended	A	B	C	D		
Standalone	L1130	1130	1064			3.2
	L1170	1170	1104		•	3.4
	L1410	1409	1344	33	33	3.8
	L1450	1449	1384		•	4.1
Line End	L1130	1128	1095			3.2
	L1170	1168	1135		•	3.4
	L1410	1408	1375	33	0	3.8
	L1450	1448	1415		•	4.1
Line Feature	L1130	1127	1127			3.2
	L1170	1167	1167		•	3.4
	L1410	1406	1406	0	0	3.8
	L1450	1446	1446		•	4.1

Suspension set contents								
SM2	SP530P BV/LE	•	•	•	•	•		
	SP530P LF			•	•		•	
SMTT	SP530P BV/LE			2x	•	•		2x
	SP530P LF			•	•		•	•
SW2	SP530P BV/LE			2x	•			
	SP530P LF			•	•		•	









- Brown **+ DA / LS**

_____ Grey **- DA**

Yellow-Green  —

Blue (N)

Black (L)

DALI 1

- Brown + DA / LS

Grey - DA

Yellow-Green  —

Blue (N)

—Black (L)

100





DALI 2

Brown

+ DA / LS

- DA

Blue




Replace 9a, b, c,




ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
SENSITIVE
DEVICES

ACL
versions only



Inrush current



I _{max} (A)	19
T _{ref} (μs)	280
Condition: Input voltage 220V	
MCB	Luminaires Max.
B-10A	15
B-13A	19
B-16A	24
B-20A	30
C-25A	37
C-10A	24
C-13A	32
C-16A	40
C-20A	49
C-25A	62