

Installation instructions

Instructions de montage

Montageanleitung

Montage instructie

Istruzioni di montaggio

Instrucciones de montaje

Instrues de montage

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi

Οδηγίες εγκατάστασης



Instrukcja montazu

Szerelési utasítások


Návod k montáži

инструкция по монтажу

Návod k montáži



				BEAM ANGLE			
				NB10	NB18	MB	WB
ST640T LED16S	1.1	23W	25W			•	•
ST640T LED25S	1.1	36W	38W			•	•
ST640T LED11S	1.1	19W	20W	•	•		
ST641T LED25S	1.1	24W	25W			•	•
ST642T LED11S	1.1	20W	21W	•	•		
ST642T LED17S	1.1	22W	23W			•	•
ST642T LED27S	1.1	36W	37W			•	•



444316005813



Version date : 29/10/2014

Data Subject to change without notice

Printed in EU


www.philips.com/lighting

Installation




ST640T
ST641T
ST642T

GA69




GLOBAL Trac Pro



ST640T 5C6
ST641T 5C6
ST642T 5C6


GAC 600



GAC
600 dali
1A 50V FELV




GLOBAL Trac Control PULSE




1.

Installation of accessories



2.



	ST640T LED I IS PSU LED driver 36W 0.3-1A 48V I 230V		ST640T LED I IS PSD Xitanium 36W/s 0.3-1A 48V TD 230V		ST640T LED I 6S PSU LED driver 36W 0.3-1A 48V I 230V		ST640T LED I 6S PSD Xitanium 36W/s 0.3-1A 48V TD 230V		ST640T LED25S PSU LED driver 36W 0.3-1A 48V I 230V		ST640T LED25S PSD Xitanium 36W/s 0.3-1A 48V TD 230V		ST641T LED25S PSU LED driver 36W 0.3-1A 48V I 230V		ST641T LED25S PSD Xitanium 36W/s 0.3-1A 48V TD 230V		ST642T LED I IS PSU LED driver 36W 0.3-1A 48V I 230V		ST642T LED I IS PSD Xitanium 36W/s 0.3-1A 48V TD 230V		ST642T LED I 7S PSU LED driver 36W 0.3-1A 48V I 230V		ST642T LED I 7S PSD Xitanium 36W/s 0.3-1A 48V TD 230V		ST642T LED27S PSU LED driver 36W 0.3-1A 48V I 230V		ST642T LED27S PSD Xitanium 36W/s 0.3-1A 48V TD 230V	
Inom(A)	0.07		0.07		0.102		0.102		0.156		0.156		0.121		0.121		0.087		0.087		0.094		0.094		0.152		0.152	
Imax(A)	6		5.3		6		5.3		6		5.3		6		5.3		6		5.3		6		5.3		6		5.3	
Tref(ms)	0.055		0.7		0.055		0.7		0.055		0.7		0.055		0.7		0.055		0.7		0.055		0.7		0.055		0.7	
MCB	Max Products*																											
B-10A	24		14		24		14		24		14		24		14		24		14		24		14		24		14	
B-16A	40		24		40		24		40		24		40		24		40		24		40		24		40		24	
C-10A	41		24		41		24		41		24		41		24		41		24		41		24		41		24	
C-16A	69		40		69		40		69		40		69		40		69		40		69		40		69		40	

* According to: IEC60555 test conditions