

4500 lm/4ft w/ 75% Down Kit*

3000/3500/4000K






| Project: | | |
|-------------|-----------|--|
| Spec Type: | | |
| Catalog No: | 24x5LxCAG | |
| Qty | | |
| Line Notes: | | |

With FloatPlane LED, it's easier than ever to integrate sleek and sporty style into your layout and within budget. Fresh and playful, with Curve and Edge profile options, FloatPlane's performance rivals that of high-end LED luminaires with the affordability of fluorescent. Available tunable white technology gives you the ability to vary color temperature and intensity, harmonizing lighting with your daily life.

Ordering guide



| Mounting Hardware | | | |
|-------------------------------|--|---------|---|
| Mount Type Consult separate m | nounting spec sheet for mount type options | • | cion Length om ceiling to top of luminaire in inches |
| Endcaps - | | Options | & Integrated Controls Please indicate with check mark. |
| 7 ¹⁵ /16" [202mm] | 7 ¹⁵ /16" [202mm] | | Dust Cover |
| | | | Response Daylight Single Zone (DS) |
| Edge 1 3/16" [30mm] | Curve 1 3/16" [30mm] | | SpaceWise DT Occupancy & Daylight Sensor (SZ) |







^{*} Nominal values within a range. Down kits and dust covers reduce output & efficacy. Consult photometry data for color temp, lumens & distribution of chosen configuration.

[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

4500 lm/4ft w/ 75% Down Kit* 3000/3500/4000K

Optical System

White light emitted from dual linear arrays of lateral-facing LEDs is diffused and redirected into the upper and lower hemispheres with a combination of high reflectivity elements and acrylic diffusers. This delivers a highly efficient 70% up / 30% down indirect/direct distribution with a wide, homogeneous batwing distribution in the upper hemisphere. Twin polymer diffusers on the lower surface combine for an optical aperture of 5-1/2" to deliver a uniform, controlled brightness, maximizing visual comfort and luminaire efficacy. Factory or field installable variable optics kits are available to modify the distribution to 75% down or close to 100% down light. Field installable dust covers available on suspended versions.

Endcaps

Diecast aluminum endcaps in either Edge or Curve versions to match housing.

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including Pacific Aqua and Surf Yellow, available on request. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel. Approx. cross section size: 1.5"h x 8"w (suspended) or 5.7"w (wall mount).

Weight

Maximum: Suspended 3.5lb/ft, Wall 3.3lb/ft

Electrical

Factory pre-wired to section ends with quick-wire connectors

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium SR, 5-100% (for SpaceWise DT).

Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output 1400lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L80 (12k) 70,000 hrs suspended / 64,000 hrs wall. (Reported methodology)
L70 (12k) 108,000 hrs suspended / 98,000 hrs wall. (Projected methodology)

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Controls

Suspended version available with the following integrated controls:
Response daylight sensor (for single zone).
SpaceWise DT occupancy & daylight sensor w/ advanced grouping & dwell time.
SpaceWise DT commissioning via Android phone and Philips Field App. Compatible dimming wireless wall switches are available. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½' on center and within 12" of an end or joint.

Joints

Self-aligning, gasketed joining system. Access panels in the driver channel allow quick and hassle-free wiring of modules either before or after mechanical joints are completed.

Approvals

Certified to UL, CSA and IES standards. Certain suspended versions (24x5L) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: http://www.philips.com/warranties


Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


Dimensions - Cross Section





4500 lm/4ft w/ 75% Down Kit* 3000/3500/4000K

Dimensions - Modules





Optics and Styles



4500 lm/4ft w/ 75% Down Kit* 3000/3500/4000K

Photometry - 3500K





Candela Distribution

| Vertical | | Zonal | | | | |
|----------|-----|-------|-----|------|-----|--------|
| Angle | 0 | 22.5 | 45 | 67.5 | 90 | Lumens |
| 0 | 957 | 957 | 957 | 957 | 957 | 0 |
| 5 | 954 | 953 | 953 | 953 | 953 | 91 |
| 15 | 926 | 920 | 924 | 923 | 920 | 260 |
| 25 | 864 | 859 | 863 | 860 | 856 | 397 |
| 35 | 773 | 767 | 771 | 767 | 764 | 481 |
| 45 | 657 | 653 | 654 | 650 | 648 | 503 |
| 55 | 517 | 515 | 512 | 509 | 508 | 458 |
| 65 | 361 | 358 | 356 | 353 | 352 | 352 |
| 75 | 190 | 190 | 189 | 187 | 186 | 200 |
| 85 | 43 | 44 | 47 | 47 | 47 | 54 |
| 90 | 0 | 3 | 4 | 6 | 6 | 0 |
| 95 | 11 | 17 | 27 | 26 | 24 | 30 |
| 105 | 47 | 54 | 102 | 149 | 169 | 108 |
| 115 | 99 | 113 | 163 | 216 | 236 | 162 |
| 125 | 133 | 155 | 203 | 242 | 255 | 177 |
| 135 | 155 | 177 | 222 | 252 | 266 | 166 |
| 145 | 172 | 187 | 226 | 253 | 265 | 139 |
| 155 | 182 | 193 | 215 | 236 | 245 | 99 |
| 165 | 187 | 192 | 203 | 212 | 216 | 58 |
| 175 | 190 | 190 | 192 | 195 | 195 | 19 |
| 180 | 190 | 190 | 190 | 190 | 190 | 0 |

Photometry based on 4ft white luminaire. Dust covers and non-white finishes reduce delivered lumens. Custom color finishes may shift output color temperature.

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

| RCR | Ceiling: | | 8 | 0 | | | 70 | | | 50 | | 0 |
|-----|----------|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|
| NCN | Wall: | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 50 | 30 | 10 | 0 |
| 0 | | 113 | 113 | 113 | 113 | 107 | 107 | 107 | 97 | 97 | 97 | 74 |
| 1 | | 103 | 98 | 94 | 90 | 98 | 94 | 90 | 85 | 82 | 79 | 62 |
| 2 | | 94 | 86 | 79 | 73 | 89 | 82 | 76 | 74 | 69 | 65 | 52 |
| 3 | | 85 | 75 | 67 | 61 | 81 | 72 | 64 | 65 | 59 | 54 | 43 |
| 4 | | 78 | 66 | 58 | 51 | 74 | 63 | 56 | 58 | 51 | 46 | 37 |
| 5 | | 71 | 59 | 50 | 44 | 68 | 56 | 49 | 51 | 45 | 40 | 32 |
| 6 | | 66 | 53 | 44 | 38 | 62 | 51 | 43 | 46 | 40 | 35 | 28 |
| 7 | | 61 | 48 | 39 | 34 | 58 | 46 | 38 | 42 | 35 | 31 | 24 |
| 8 | | 57 | 44 | 35 | 30 | 54 | 42 | 34 | 38 | 32 | 27 | 22 |
| 9 | | 53 | 40 | 32 | 27 | 50 | 38 | 31 | 35 | 29 | 24 | 20 |
| 10 | | 49 | 37 | 29 | 24 | 47 | 35 | 28 | 32 | 26 | 22 | 18 |

Avg. Luminance (cd/m2)

| v ei ticai | 1.15 | DI IZOI ILAI 741 I) | КIС |
|------------|------|---------------------|------|
| Angle | 0 | 45 | 90 |
| 55 | 4428 | 4391 | 4355 |
| 65 | 4195 | 4145 | 4095 |
| 75 | 3615 | 3588 | 3534 |
| 85 | 2422 | 2664 | 2664 |

Distribution

| Hemisphere | 26% Up / 74% Down |
|-----------------------|-------------------|
| Spacing Along (0 °) | 1.28 |
| Spacing Across (90 °) | 1.26 |

Registration Number: F46Z-EB16M2 (7/3/2015) Model Number: 24x5LBCAG Type: Luminaire - Linear

4500 lm/4ft w/ 75% Down Kit* 3000/3500/4000K

Optical Performance

| Nominal CCT: | 3000K | 3500K | 4000K |
|-----------------|--------|--------|--------|
| Flux (lm) | 3674 | 3753 | 3782 |
| Efficacy (lm/W) | 103.2 | 105.4 | 106.2 |
| Power (W) | 35.6 | 35.6 | 35.6 |
| CCT (K) | 3028 | 3344 | 3907 |
| CRI | 81 | 82 | 83 |
| R9 | 2 | 5 | 10 |
| x | 0.4379 | 0.4178 | 0.3867 |
| у | 0.4097 | 0.4036 | 0.3864 |
| Duv | 0.0020 | 0.0030 | 0.0030 |

Electrical Performance - 3500K

| Input Voltage | 120V | 277V | 347V |
|------------------------|-------|-------|-------|
| Input Power | 35.6W | 34.9W | 30.2W |
| Input Current | 0.30A | 0.13A | 0.09A |
| Power Factor | 0.990 | 0.980 | 0.956 |
| Total Harm. Distortion | 6.0% | 12.9% | 11.0% |

Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).

