

SGP618/SGP619

Mounting instruction

Instructions de montage

Montageanleitung

Montage instructie

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi


Οδηγίες συναρμολόγησης


Instrukcja montazu

Szerelési utasítások

Návod k montáži

Монтажная инструкция




							TYPE
CPO-W	60	CDM-T	35	7-10	0.13max	0.069	SGP618
CPO-W	140	CDM-T	70	7-10	0.13max	0.069	SGP618
CPO-G	65	CDM-T	150	7-10	0.13max	0.069	SGP618
CPO-G	140	CD0-TT	70	7-10	0.13max	0.069	SGP618
CDO-TT	100	CDO-TT	150	7-10	0.13max	0.069	SGP618
CDO-ET	70	CDO-ET	100	7-10	0.13max	0.069	SGP618
		CDO-ET	150	7-14	0.14max	0.069	SGP618/SGP619
		CDO-EV	250	11-14	0.14max	0.054	SGP619
		CDO-EV	400	11-14	0.14max	0.054	SGP619
SON-E	50	SON-T	50	7-10	0.13max	0.069	SGP618
SON-E	70	SON-T	70	7-10	0.13max	0.069	SGP618
SON-E	100	SON-T	100	7-10	0.13max	0.069	SGP618
		SON-T	150	7-14	0.14max	0.069	SGP618/SGP619
SON-T	400	SON-T	250	11-14	0.14max	0.054	SGP619
		SON-T	600	11-14	0.14max	0.054	SGP619
		SON-E	150	7-14	0.14max	0.069	SGP618/SGP619
		SON-E	250	11-14	0.14max	0.054	SGP619
		SON-E	400	11-14	0.14max	0.054	SGP619
		PL-T	32	7-10	0.13max	0.069	SGP618
PL-T	57	PL-T	42	7-10	0.13max	0.069	SGP618
		PL-H	60	7-10	0.13max	0.069	SGP618
		PL-H	85	7-10	0.13max	0.069	SGP618
		PL-H	120	11-14	0.14max	0.054	SGP619
HPLN	50	HPLN	80	7-10	0.13max	0.069	SGP618
		HPLN	125	7-10	0.13max	0.069	SGP618
HPLN	250	HPLN	400	11-14	0.14max	0.054	SGP619
HQI-E	70	HQI-T	70	7-10	0.13max	0.069	SGP618
HQI-E	100	HQI-T	150	7-10	0.13max	0.069	SGP618
HQI-E	150	HQI-T	250	11-14	0.14max	0.054	SGP619
		HQI-T	400	11-14	0.14max	0.054	SGP619


Ambient Temperature: -20 to +30 °C in general.

SGP618 LUMINAIRE DIMENSION


SGP618 SIP
SGP618 DIP
0.10m²



SGP618 SIP
SGP618 DIP
0.12m²




SGP618 SIP
SGP618 DIP
0.13m²




SGP619 LUMINAIRE DIMENSION

SGP619 SIP
SGP619 DIP
0.11m²



SGP619 SIP
SGP619 DIP
0.14m²




1


LANTERN CONNECTION VARIANTS

1a


Knife Connector




Class I (top picture) and
Class II (bottom picture) Knife connector



Knife connector with photocell




Wieland Connector Class II (left-side picture)




Wieland Connector Class I (right-side picture)

2


MOUNTING OF THE LANTERN




Post Top Mounting (left-side picture)
and Side Entry Mounting (right-side picture)




Power-Line Connection



Gear Tray de-mounting (left side) and
Lamp Mounting for E40/E27/PGZI2/GI2 (right side)



Lamp Mounting for Fluo Compact (left-side picture) and
Horizontal Alignment (right-side picture)



Vertical Alignment (left-side picture) and
Luminary Closing (right-side picture)

3

LANTERN LABELS

