













Philips Lighting
www.philips.com

4422 002 82224
04/14
Printed in EU
Data subject to change



Use Philips lamps for optimum performance
Funzionamento ottimale garantito con lampade Philips
Resultados óptimos con lámparas Philips
Toimii parhaiten Philips-lamppujen kanssa
Funciona melhor com lâmpadas Philips no interior
Werk het best met Philips-lampen

Fonctionnement optimal avec lampes Philips
Bestes Betriebsergebnis mit Philips-Lampen
Fungerer bedst med Philips-lamper
Fungerer mest optimalt med Philips-lamper
Fungerar bäst med lampor från Philips

PHILIPS

SmartForm TBS460/462/464/465/467

Installation instructions

Instructions de montage
Montageanleitung
Montage instruktie
Istruzioni di montaggio

Instrucciones de montaje
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergeleri
Οδηγίες συναρμολόγησης
Instrukcja montażu

Szerelési utasítások
Návod k montáži
ИНСТРУКЦИЯ ПО МОНТАЖУ
Návod k montáži


IP 20 - IP 40

This luminaire must be earthed.
Ce luminaire doit être mis à la terre.
Diese Leuchte muß geerdet werden.
Dit armatuur moet worden geaard.
Questa armatura deve essere collegata a terra.
La Luminaria debe estar conectada a tierra.


For EL-versions:
NO INSULATION



Class I




		mm	A	B	C	D	E	F	
Module 600	TBS460	14/24V	597	597	574	574	45	59	
	TBS460	28/54V	1197	297	1174	274	45	59	
	TBS460	35/49/80V	1497	297	1474	274	45	59	
	TBS464	14/24V	597	597	574	574	47	65	
	TBS464	28/54V	1197	297	1174	274	47	65	
Module 625	TBS464	35/49/80V	1497	297	1474	274	47	65	
	TBS462	14/24V	622	622	574	574	45	59	
	TBS462	28/54V	1247	309.5	1174	274	45	59	
	TBS462	35/49/80V	1559.5	309.5	1474	274	45	59	
	TBS465	14/24V	622	622	574	574	47	65	
Module 675	TBS465	28/54V	1247	309.5	1174	274	47	65	
	TBS465	35/49/80V	1559.5	309.5	1474	274	47	65	
	TBS467	14/24V	673	673	574	574	47	65	only lay-in




PHILIPS


Lay-In




ZBS460 SMB-TPM




ZBS460 SMB (4 Pcs.)




ZBS460 SMB-PLC




Wieland/Adels (W)



Wago (WA)



ENSTO (EN)



Push-In (PI)

