



TMX204 LS

TMX204 2xTL-D36W HFR CFL

TMX204 LS, 2, MASTER TL-D, 36 W, HF Regulator, Floating connector

TMX204 LS is a functional batten for TL-D and TL5 fluorescent lamps for general lighting. A wide range of reflectors and attachments from the TTX400 series can be fitted to enhance system efficiency and versatility, making it suitable for a variety of applications. This batten can be suspended or surface-mounted. Thanks to its slim design, it is also well suited for build-in applications and coves.

Product data


General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFR [HF Regulator]
Product family code	TMX204 [TMX204 LS]
Embedded control	-
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Light Technical	
Number of light sources	2
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	36 W
Connection	Floating connector

Mechanical and Housing	
Fixation point length distance (Nom)	650 mm
Overall length	1,226 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TMX204 2xTL-D36W HFR CFL
Full product name	TMX204 2xTL-D36W HFR CFL
Full product code	871155910066199
Order code	910400661418
Material Nr. (12NC)	910400661418
Numerator - Quantity Per Pack	1

TMX204 LS

EAN/UPC - Product/Case	8711559100661
Numerator - Packs per outer box	5
EAN/UPC - Case	8711559100678

Dimensional drawing



Product
TMX204 2xTL-D36W HFR CFL

