



Phoenix HDK900

MDK900 HPI-P250W-BU IC

MASTER HPI Plus, 250 W

A sturdy long lasting quality electrical gear housing of compact and elegant design, suitable to give together with a range of reflector types and attachments, the right solution for low and high bay lighting requirement.

Product data

General Information	
Lamp family code	HPI-P [MASTER HPI Plus]
Gear	CONV [Conventional]

Light Technical	
Number of light sources	1
Optic type	-

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	250 W

Approval and Application	
Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]

Product Data	
Order product name	MDK900 HPI-P250W-BU IC
Full product name	MDK900 HPI-P250W-BU IC
Full product code	910401240780
Order code	01240780
Material Nr. (12NC)	910401240780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Phoenix HDK900

Dimensional drawing

