



# Tango MMF383

## MMF383 SON-T400W 220V WB BK

SON-T, 400 W, Wide beam

A compact and sturdy family of floodlights complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. Its all-weather construction is designed for simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	- [-]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	400 W

Mechanical and Housing	
Housing Color	Black
Product Data	
Order product name	MMF383 SON-T400W 220V WB BK
Full product name	MMF383 SON-T400W 220V WB BK
Full product code	910401604880
Order code	910401604880
Material Nr. (12NC)	910401604880
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# Tango MMF383

## Dimensional drawing

