



# Tango MMF283

## MMF283 MHN-TD70W 220V-50Hz WB YE

MHN-TD, 70 W, Wide beam

Compact, sturdy floodlight complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. All-weather construction designed for simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	MHN-TD
Cap-Base	- [-]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	70 W
Mechanical and Housing	
Housing Color	Yellow

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MMF283 MHN-TD70W 220V-50Hz WB YE
Full product name	MMF283 MHN-TD70W 220V-50Hz WB YE
Full product code	910401630380
Order code	910401630380
Material Nr. (12NC)	910401630380
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Tango MMF283

### Dimensional drawing

