



# Halolite

## QVF133 HAL-TDS150W 220V-50Hz

Plusline Small (double-ended), 150 W

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

### Product data

General Information	
Lamp family code	HAL-TDS [Plusline Small (double-ended)]
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	150 W
Product Data	
Order product name	QVF133 HAL-TDS150W 220V-50Hz

Full product name	QVF133 HAL-TDS150W 220V-50Hz
Full product code	910401631180
Order code	910401631180
Material Nr. (12NC)	910401631180
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163289168
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163181455

## Dimensional drawing

