



Halolite

QVF135 HAL-TDS500W 220V-50Hz

Plusline Small (double-ended), 500 W

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

Product data

General Information	
Lamp family code	HAL-TDS [Plusline Small (double-ended)]
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	500 W
Product Data	
Order product name	QVF135 HAL-TDS500W 220V-50Hz

Full product name	QVF135 HAL-TDS500W 220V-50Hz
Full product code	910401631280
Order code	910401631280
Material Nr. (12NC)	910401631280
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163289175
Numerator - Packs per outer box	12

Halolite

Dimensional drawing

