



MVF616 C New Decoflood

MVF616 CMHN-TD150W K 220V-50Hz MB

MHN-TD, 150 W, Medium beam

A medium-sized, high-grade floodlight with a choice of light distributions from a variety of lamps. It is well suited to city environments. Its all-weather construction is designed for simple cleaning and speedy servicing.

Product data

General Information	
Lamp family code	MHN-TD
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Medium beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	150 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MVF616 CMHN-TD150W K 220V-50Hz MB
Full product name	MVF616 CMHN-TD150W K 220V-50Hz MB
Full product code	910401636380
Order code	910401636380
Material Nr. (12NC)	910401636380
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

MVF616 C New Decoflood

Dimensional drawing

