



Landmark MVF028

MVF028 MHN-LA1000W 220-240V WB

MASTER MHN-LA, 1000 W

A high-performance general-purpose floodlight for sports lighting, general area lighting and facade illumination. This compact unit distributes a well-controlled, low glare, wide, medium or narrow beam evenly, accurately and efficiently. Excellent lighting results are achieved with the double-ended 2000W metal-halide lamp and also with standard 1000W metal-halide or high-pressure sodium lamps. Rugged all-weather construction designed for easy aiming, simple cleaning and speedy servicing.

Product data

General Information	
Lamp family code	MHN-LA [MASTER MHN-LA]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 Hz
Power Consumption	1,000 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MVF028 MHN-LA1000W 220-240V WB
Full product name	MVF028 MHN-LA1000W 220-240V WB
Full product code	910401639280
Order code	910401639280
Material Nr. (12NC)	910401639280
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Landmark MVF028

Dimensional drawing

