



Landmark MVF028

MVF028 MHN-LA2000W 380-415V WB

MASTER MHN-LA, 2000 W, Wide beam

A high-performance general-purpose floodlight for sports lighting, general area lighting and facade illumination. This compact unit distributes a well-controlled, low glare, wide, medium or narrow beam evenly, accurately and efficiently. Excellent lighting results are achieved with the double-ended 2000W metal-halide lamp and also with standard 1000W metal-halide or high-pressure sodium lamps. Rugged all-weather construction designed for easy aiming, simple cleaning and speedy servicing.

Product data

General Information	
Lamp family code	MHN-LA [MASTER MHN-LA]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	380 to 415 V
Power Consumption	2,000 W
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Product Data	
Order product name	MVF028 MHN-LA2000W 380-415V WB
Full product name	MVF028 MHN-LA2000W 380-415V WB
Full product code	910401639480
Order code	910401639480
Material Nr. (12NC)	910401639480
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Landmark MVF028

Dimensional drawing

