



# Optivision MVP507 C

## MVP507 CSON-T1000W 220-240V WB

SON-T, 1000 W, Wide beam

An asymmetric luminaire for down lighting that combines a compact design with very high efficiency. It provides excellent spill-light control and limitation of glare and upward leakage of light. It accommodates metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Available with narrow, medium and wide beams.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	SGR [SON gear]

  

Light Technical	
Number of light sources	1
Light source color	-
Optic type outdoor	Wide beam

  

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 Hz
Power Consumption	1,000 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

  

Product Data	
Order product name	MVP507 CSON-T1000W 220-240V WB
Full product name	MVP507 CSON-T1000W 220-240V WB
Full product code	910401647680
Order code	01647680
Material Nr. (12NC)	910401647680
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# Optivision MVP507 C

## Dimensional drawing

