



Optivision MVP507 C

MVP507 CMHN-LA2000W 380-415V MB

MASTER MHN-LA, 2000 W, Medium beam

An asymmetric luminaire for down lighting that combines a compact design with very high efficiency. It provides excellent spill-light control and limitation of glare and upward leakage of light. It accommodates metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Available with narrow, medium and wide beams.

Product data

General Information		Approval and Application	
Lamp family code	MHN-LA [MASTER MHN-LA]	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Gear	CONV [Conventional]	Product Data	
Light Technical		Order product name	MVP507 CMHN-LA2000W 380-415V MB
Number of light sources	1	Full product name	MVP507 CMHN-LA2000W 380-415V MB
Light source color	-	Full product code	910401647980
Optic type outdoor	Medium beam	Order code	910401647980
Operating and Electrical		Material Nr. (12NC)	910401647980
Input Voltage	380 to 415 V	Numerator - Quantity Per Pack	1
Line Frequency	50 Hz	Numerator - Packs per outer box	1
Power Consumption	2,000 W		

Optivision MVP507 C

Dimensional drawing

