



# ConTempo 150-250-350

## RVP350 HPI-T400W IC 220V-50Hz A SP

MASTER HPI-T Plus, 400 W, Asymmetrical

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

### Product data

| General Information      |                            |
|--------------------------|----------------------------|
| Lamp family code         | HPI-TP [MASTER HPI-T Plus] |
| Cap-Base                 | E40 [E40]                  |
| Gear                     | CONV [Conventional]        |
| Light Technical          |                            |
| Number of light sources  | 1                          |
| Optic type outdoor       | Asymmetrical               |
| Operating and Electrical |                            |
| Input Voltage            | 220 V                      |
| Line Frequency           | 50 Hz                      |
| Power Consumption        | 400 W                      |

| Approval and Application        |  |
|---------------------------------|--|
| Ingress protection code         | IP65 [Dust penetration-protected, jet-proof] |
| Product Data                    |  |
| Order product name              | RVP350 HPI-T400W IC 220V-50Hz A SP           |
| Full product name               | RVP350 HPI-T400W IC 220V-50Hz A SP           |
| Full product code               | 910401649480                                 |
| Order code                      | 910401649480                                 |
| Material Nr. (12NC)             | 910401649480                                 |
| Numerator - Quantity Per Pack   | 1  |
| Numerator - Packs per outer box | 1  |

## ConTempo 150-250-350

### Dimensional drawing

