



Powervision MVF024 C

MVF024 C 1xSON-T1000W WB

1, SON-T, 1000 W, Wide beam

The high-performance general-purpose floodlight for sports lighting, general area lighting and facade illumination. This compact unit distributes a well-controlled, low glare, wide, medium or narrow beam evenly, accurately and efficiently. Excellent lighting results are achieved with the double-ended 2000W metal-halide lamp which is developed in parallel with the floodlight and also with standard 1000W metal-halide or high-pressure sodium lamps. Rugged all weather construction designed for easy aiming, simple cleaning and speedy servicing.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E40 [E40]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	1,000 W
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Product Data	
Order product name	MVF024 C 1xSON-T1000W WB
Full product name	MVF024 C 1xSON-T1000W WB
Full product code	910401804180
Order code	910401804180
Material Nr. (12NC)	910401804180
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291993520
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291993520

Powervision MVF024 C

Dimensional drawing

