



Malaga SGS102

SGS102 MAX250W-E40 II MR-AS 42/60

MALAGA, E40, Safety class II, Moveable reflector with Allen screw, Universal for diameter 42 to 60 mm

Malaga is a versatile road-lighting luminaire. It offers modern styling and quality lighting for safe and comfortable driving, and for area illumination, with low investment and maintenance costs. The optical system has been designed to deliver good beam control and light output. Malaga provides optimal illuminance and good uniformity when the mounting height approximately equals the road width and the mast spacing is approximately 3.5 times the road width. It is suitable for post-top and side-entry mounting; a wall-mounting bracket is also available.

Product data

General Information	
Cap-Base	E40 [E40]
Photocell	-
Product family code	SGS102 [MALAGA]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Number of light sources	1
Optic type outdoor	Moveable reflector with Allen screw
Mechanical and Housing	
Mounting device	Universal for diameter 42 to 60 mm
Approval and Application	
Mech. impact protection code	IK08 [5 J vandal-protected]

Protection class IEC	Safety class II
Product Data	
Order product name	SGS102 MAX250W-E40 II MR-AS 42/60
Full product name	SGS102 MAX250W-E40 II MR-AS 42/60
Full product code	871155927098200
Order code	910401906612
Material Nr. (12NC)	910401906612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559270982
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559270982

Malaga SGS102

Dimensional drawing

