



Tango MMF383

MMF383 HPI-TP250W 220V WB YE

MASTER HPI-T Plus, 250 W, Wide beam

A compact and sturdy family of floodlights complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. Its all-weather construction is designed for simple cleaning and speedy servicing.

Product data

General Information	
Lamp family code	HPI-TP [MASTER HPI-T Plus]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	250 W

Mechanical and Housing	
Housing Color	Yellow
Product Data	
Order product name	MMF383 HPI-TP250W 220V WB YE
Full product name	MMF383 HPI-TP250W 220V WB YE
Full product code	910401965280
Order code	910401965280
Material Nr. (12NC)	910401965280
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Tango MMF383

Dimensional drawing

