



# Pacific II TCW097

## TCW097 1xTL5-28W HFA 220V 50Hz

1, TL5, 28 W, HF standard for TL5, 220 V, 50 Hz

Functional impact-, dust- and jetproof luminaire for single and twin TLD and TL5 fluorescent lamps for indoor applications and semioutdoor applications. Housing and cover of TCW097 are made of high quality poly-carbonate which has an excellent impact resistant property. The cover has anti-UV additives which bring additional performance levels to UV protection. Available with conventional or high-frequency (HF) electronic control gears. Can be ceiling mounted or suspended. Equipped with mounting brackets, mounting is made easy via screws without drilling into the luminaire housing. Gear tray and metal toggles are re-installed; cable gland and mounting brackets are delivered with the luminaire.


### Product data

General Information	
Lamp family code	TL5 [TL5]
Number of gear units	1 unit
Gear	HFA [HF standard for TL5]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	28 W
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Protection class IEC	
Safety class I	
Product Data	
Order product name	TCW097 1xTL5-28W HFA 220V 50Hz
Full product name	TCW097 1xTL5-28W HFA 220V 50Hz
Full product code	910401984280
Order code	910401984280
Material Nr. (12NC)	910401984280
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291993629
Numerator - Packs per outer box	6

# Pacific II TCW097

## Dimensional drawing



TCW097	118 114	136 128	158 135	218 214	236 228	258 235
LxWxH(mm)	660x100x110	1270x100x110	1570x100x110	660x150x110	1270x150x110	1570x150x110

