



Lineco TMS022

TMS022 1xTL-D58W/840 HFRUK

TMS022, 1, MASTER TL-D, 58 W, 840 neutral white, HF Regulator

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFR [HF Regulator]
Product family code	TMS022 [TMS022]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
Light Technical	
Number of light sources	1
Light source color	840 neutral white
Optic type	-
Operating and Electrical	
Input Voltage	230 to 240 V


Power Consumption	58 W
Mechanical and Housing	
Fixation point length distance (Nom)	300 mm
Overall length	462 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TMS022 1xTL-D58W/840 HFRUK
Full product name	TMS022 1xTL-D58W/840 HFRUK

Lineco TMS022

Full product code	871155911706500
Order code	11706500
Material Nr. (12NC)	910402204284
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559117065

Numerator - Packs per outer box	1
EAN/UPC - Case	8711559117065

Dimensional drawing



Product	TMS022 1xTL-D58W/840 HFRUK
---------	----------------------------

