



Lineco TMS022

TMS022 1xTL-D58W/840 HFRUK

TMS022 - 1 pc - MASTER TL-D - 58 W - 840 neutral white - HF Regulator - United Kingdom

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	TL-D [MASTER TL-D]
Lamp power	58 W
Light source colour	840 neutral white
Kombipack	Lamp(s) included
Compensation circuit	-
Gear	HFR [HF Regulator]
Optic type	No [-]
Emergency lighting	No [-]
Protection class IEC	Safety class I (I)
Ready-to-install	-
Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Flammability mark	F [For mounting on normally flammable surfaces]
Country version	UK [United Kingdom]
CE mark	CE mark
ENEC mark	ENEC mark

Product family code	TMS022 [TMS022]
Operating and Electrical	
Input Voltage	230 to 240 V
Mechanical and Housing	
Housing configuration	No [-]
Fixation point length distance (nom.)	300 mm
Overall length	462 mm
Dimensions (height x width x depth)	NaN x NaN x 462 mm (NaN x NaN x 18.2 in)
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Lineco TMS022

Application Conditions

Suitable for random switching Not applicable


Product Data

Full product code 871155911706500
Order product name TMS022 1xTL-D58W/840 HFRUK
EAN/UPC – product 8711559117065
Order code 11706500

SAP numerator – quantity per pack 1
Numerator – packs per outer box 1
SAP material 910402204284
Net Weight (Piece) 1.600 kg



Dimensional drawing



TMS022

