



# Lineco TMS022

## TMS022 1xTL-D58W HF

TMS022 - 1 pc - MASTER TL-D - 58 W - Electronic high-frequency

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

### Product data

General Information		Product family code	
Number of light sources	1 [ 1 pc]	TMS022 [ TMS022]	
Lamp family code	TL-D [ MASTER TL-D]	Operating and Electrical	
Lamp power	58 W	Input Voltage	230 to 240 V
Kombipack	-	Mechanical and Housing	
Compensation circuit	-	Housing configuration	No [ -]
Gear	HF [ Electronic high-frequency]	Fixation point length distance (nom.)	900 mm
Optic type	No [ -]	Overall length	1525 mm
Emergency lighting	No [ -]	Dimensions (height x width x depth)	NaN x NaN x 1525 mm (NaN x NaN x 60 in)
Protection class IEC	Safety class I (I)	Approval and Application	
Ready-to-install	-	Ingress protection code	IP20 [ Finger-protected]
Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]	Mech. impact protection code	IK02 [ 0.2 J standard]
Flammability mark	F [ For mounting on normally flammable surfaces]		
Country version	NO [ Norway]		
CE mark	CE mark		
ENEC mark	ENEC mark		

# Lineco TMS022

## Application Conditions

Suitable for random switching Not applicable


## Product Data

Full product code 871829104533599  
Order product name TMS022 1xTL-D58W HF  
EAN/UPC – product 8718291045335  
Order code 04533599

SAP numerator – quantity per pack 1  
Numerator – packs per outer box 9  
SAP material 910402269603  
Net Weight (Piece) 1.244 kg



## Dimensional drawing



TMS022

