



# Lineco TMS022

## TMS022 2xTL-D58W HF

TMS022 - 2 pcs - MASTER TL-D - 58 W - Electronic high-frequency

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

### Product data

General Information	
Number of light sources	2 [ 2 pcs]
Lamp family code	TL-D [ MASTER TL-D]
Lamp power	58 W
Kombipack	-
Compensation circuit	-
Gear	HF [ Electronic high-frequency]
Optic type	No [-]
Emergency lighting	No [-]
Protection class IEC	Safety class I (I)
Ready-to-install	-
Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Flammability mark	F [ For mounting on normally flammable surfaces]
Country version	NO [ Norway]
CE mark	CE mark
ENEC mark	ENEC mark

Product family code	TMS022 [ TMS022]
Operating and Electrical	
Input Voltage	230 to 240 V
Mechanical and Housing	
Housing configuration	No [-]
Fixation point length distance (nom.)	900 mm
Overall length	1525 mm
Dimensions (height x width x depth)	NaN x NaN x 1525 mm (NaN x NaN x 60 in)
Approval and Application	
Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]

# Lineco TMS022

## Application Conditions

Suitable for random switching Not applicable


## Product Data

Full product code 871829104534299  
Order product name TMS022 2xTL-D58W HF  
EAN/UPC – product 8718291045342  
Order code 04534299

SAP numerator – quantity per pack 1  
Numerator – packs per outer box 6  
SAP material 910402269703  
Net Weight (Piece) 1.300 kg



## Dimensional drawing



TMS022

