



TCW060

TCW060 2xTL5-49W HFP

TCW060, 2, TL5, 49 W, HF Performer


Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Product family code	TCW060 [TCW060]
CE mark	Yes
Glow-wire test	Temperature 650 °C, duration 5 s
Light Technical	
Number of light sources	2
Optical cover type	Polycarbonate bowl/cover prismatic
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	49 W
Connection	Screw connection block 3-pole
Mechanical and Housing	
Fixation point length distance (Nom)	1,000 mm
Housing Color	Grey

Overall length	1,515 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Application Conditions	
Suitable for random switching	Yes
Product Data	
Order product name	TCW060 2xTL5-49W HFP
Full product name	TCW060 2xTL5-49W HFP
Full product code	872790063872100
Order code	910402499612
Material Nr. (12NC)	910402499612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900638721
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900638721

Dimensional drawing



Product	A	B
TCW060 2xTL5-49W HFP	1,000 mm	1,515 mm

