



ComfortVision SNF111

SNF111 1xHPI-TP1000W K NB

COMFORTVISION, 1, MASTER HPI-T Plus, 1000 W, Narrow beam

ComfortVision is a high-efficiency, asymmetric floodlight, distributing a low-glare beam evenly and accurately. It can accommodate metal-halide lamps for good color rendering or a high-pressure sodium lamp for economical performance. Available in medium- or narrow-beam versions, the floodlight accepts a single 1000 or two 400 or 600 W lamps. The twin-lamp version offers switching flexibility that permits tailoring to the user's needs while allowing energy savings. ComfortVision's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing. For optimal downlighting, the luminaire should be mounted horizontally at a height of 15-25 meters. It has an adjustment range of $\pm 12^\circ$ from the horizontal. A universal mounting bracket allows mounting to headframes, ceilings and walls.

Product data

| General Information | |
|--------------------------|----------------------------|
| Lamp family code | HPI-TP [MASTER HPI-T Plus] |
| Gear | CONV [Conventional] |
| Product family code | SNF111 [COMFORTVISION] |
| CE mark | Yes |
| ENEC mark | - |
| Light Technical | |
| Number of light sources | 1 |
| Optic type outdoor | Narrow beam |
| Operating and Electrical | |
| Power Consumption | 1,000 W |

| Approval and Application | |
|---------------------------------|--|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Protection class IEC | Safety class I |
| Product Data | |
| Order product name | SNF111 1xHPI-TP1000W K NB |
| Full product name | SNF111 1xHPI-TP1000W K NB |
| Full product code | 871155954752700 |
| Order code | 910403029212 |
| Material Nr. (12NC) | 910403029212 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711559547527 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8711559547527 |

Dimensional drawing

