



# ComfortVision SNF111

## SNF111 1xHPI-TP1000W K MB

COMFORTVISION, 1, MASTER HPI-T Plus, 1000 W, Medium beam

ComfortVision is a high-efficiency, asymmetric floodlight, distributing a low-glare beam evenly and accurately. It can accommodate metal-halide lamps for good color rendering or a high-pressure sodium lamp for economical performance. Available in medium- or narrow-beam versions, the floodlight accepts a single 1000 or two 400 or 600 W lamps. The twin-lamp version offers switching flexibility that permits tailoring to the user's needs while allowing energy savings. ComfortVision's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing. For optimal downlighting, the luminaire should be mounted horizontally at a height of 15–25 meters. It has an adjustment range of  $\pm 12^\circ$  from the horizontal. A universal mounting bracket allows mounting to headframes, ceilings and walls.

### Product data

General Information		Operating and Electrical	
Lamp family code	HPI-TP [MASTER HPI-T Plus]	Power Consumption	1,000 W
Gear	CONV [Conventional]	Approval and Application	
Product family code	SNF111 [COMFORTVISION]	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
CE mark	Yes	Protection class IEC	Safety class I
ENEC mark	-	Product Data	
Light Technical		Order product name	SNF111 1xHPI-TP1000W K MB
Number of light sources	1	Full product name	SNF111 1xHPI-TP1000W K MB
Optic type outdoor	Medium beam	Full product code	871155954753400
		Order code	910403029312
		Material Nr. (12NC)	910403029312

ComfortVision SNF111

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559547534
Numerator - Packs per outer box	1

EAN/UPC - Case	8711559547534
----------------	---------------

Dimensional drawing

