



# PowerVision MVF024

## MVF024 MHN-LA2000W/842 400V NB SI

POWERVERSION, MASTER MHN-LA, 2000 W, Narrow beam

PowerVision is a high-performance general-purpose floodlight for sports lighting, general area lighting and facade illumination. This compact luminaire distributes a low-glare, wide, medium or narrow beam evenly, accurately and efficiently. With the MHN-LA 2000W/842 lamp, the natural color rendering (Ra = 80) and comfortable atmosphere (Tc = 4200 K) are well suited to TV and filming. With the MHN-LA 2000W/956 lamp, the highest international CTV requirements (Ra = 90, Tc = 5600 K) are met. A built-in skirt in the reflector assembly minimizes spill light and glare. Integrated system of optics, gear and lamp in a single housing, ensuring high beam efficiency and a well-controlled beam. Built-in skirt in reflector assembly minimizes spill light and glare. The luminaire's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing.

### Product data

<b>General Information</b>		<b>Power Consumption</b>	
Lamp family code	MHN-LA [MASTER MHN-LA]	2,000 W	
Gear	CONV [Conventional]		
Product family code	MVF024 [POWERVERSION]	<b>Mechanical and Housing</b>	
CE mark	Yes	Housing Color	
ENEC mark	ENEC mark	-	
		<b>Approval and Application</b>	
<b>Light Technical</b>		Ingress protection code	
Number of light sources	1	IP55 [Dust accumulation-protected, jet-proof]	
Light source color	842 neutral white	Protection class IEC	
Optic type outdoor	Narrow beam	Safety class I	
		<b>Product Data</b>	
<b>Operating and Electrical</b>		Order product name	
Input Voltage	400 V	MVF024 MHN-LA2000W/842 400V NB SI	
		Full product name	
		MVF024 MHN-LA2000W/842 400V NB SI	
		Full product code	
		871155954782400	
		Order code	
		910403032212	

PowerVision MVF024

Material Nr. (12NC)	910403032212
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559547824
Numerator - Packs per outer box	1

EAN/UPC - Case	8711559547824
----------------	---------------

Dimensional drawing

