



# SmartForm TBS417

## ZBS417 EP-T SET

TBS415 ACC, White

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m<sup>2</sup> is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO<sub>2</sub> levels, making SmartForm an environmentally friendly choice. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

### Product data

General Information			
Accessory color	White	Order code	910403204303
Product family code	ZBS417 [TBS415 ACC]	Material Nr. (12NC)	910403204303
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8717943984381
		Numerator - Packs per outer box	16
		EAN/UPC - Case	8717943984398
Product Data			
Order product name	ZBS417 EP-T SET		
Full product name	ZBS417 EP-T SET		
Full product code	871794398438199		