



# SmartForm TBS417

## ZBS417 EP-A SET

TBS415 ACC, White

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient LED or TL5 light sources and a range of Philips electronic ballasts, the SmartForm recessed family can be equipped with lighting controls for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense) in order to reduce energy consumption (W/m2 is very low). In this way, this Green Flagship range also reduces the overall cost of ownership as well as CO2 levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS417 – 'light line beam'. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. 'Light line beam' TBS417 1-lamp. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. 'Light line beam' TBS417 2-lamps. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

### Product data

General Information			
Accessory color	White	Full product code	871794398440499
Product family code	ZBS417 [TBS415 ACC]	Order code	910403204403
		Material Nr. (12NC)	910403204403
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8717943984404
		Numerator - Packs per outer box	20
		EAN/UPC - Case	8717943984411
Product Data			
Order product name	ZBS417 EP-A SET		
Full product name	ZBS417 EP-A SET		

